## **Product Specification PDF**



| Date              | Correct as of 4th Mar 2019 |  |  |
|-------------------|----------------------------|--|--|
| Brand             | -                          |  |  |
| Product           | T49162D                    |  |  |
| Description       | Dex S/Driver SL/PH Set/7   |  |  |
| Barcode           | 5013969245110              |  |  |
| Commodity code    | -                          |  |  |
| Country of origin | -                          |  |  |



Features & Benefits DEXTRO PREMIUM QUALITY VDE SCREWDRIVERS ~ Precision machined tip for an exact screw fit & damage free

screwdriving. ~ Premium quality Chrome Vanadium steel blade for exceptional strength & durability. ~ Long fine neck for precise fingertip control. ~ Handle injection moulded directly to blade giving the ultimate bond for increased reliability & durability. ~ Ergonomically shaped, dual component handle for increased comfort, control & safety. ~ Ridges along the head give extra grip in that last ¼ turn. ~ Tip type marking for easy identification.

Applicable Standards IEC 60900 VDE 0682-201 ISO 2380 -2, DIN ISO 8764

Health & Safety Users are advised to regularly examine their VDE tools, Even the slightest damage can compromise the insulation

integrity and potentially expose the user to the risk of injury or even death

Warranty C.K products are guaranteed for 1 year against imperfect materials or workmanship. Damage caused through

normal wear and tear or resulting from inappropriate use, is not covered.

| Product Weights and Measures |              |                             |                     |                   |  |
|------------------------------|--------------|-----------------------------|---------------------|-------------------|--|
|                              | Product only | Product & primary packaging | Secondary packaging | Transit packaging |  |
| Item Quantity                | 1            | 1                           | 0                   | 18                |  |
| Width mm                     | 223          | 223                         | 0                   | 600               |  |
| Depth mm                     | 38           | 38                          | 0                   | 430               |  |
| Height mm                    | 320          | 320                         | 0                   | 260               |  |
| Weight                       | 465          | 659                         | 0                   | 12462             |  |
| Packaging Information        | Card use     | Box                         | 0                   | Case              |  |
|                              | Card gms     | 190                         | 0                   | 400               |  |
|                              | Plastic use  | Film                        | 0                   | -                 |  |
|                              | Plastic gms  | 4                           | 0                   | 0                 |  |
|                              | Metal use    | 0                           | 0                   | -                 |  |
|                              | Metal gms    | 0                           | 0                   | 0                 |  |
|                              | Timber use   | 0                           | 0                   | -                 |  |
|                              | Timber gms   | 0                           | 0                   | 0                 |  |