

MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it



Technical Datasheet

tasker® C113 - 1x0,25 mm² - Spiral Shielded Cable



A	B	C	D
---	---	---	---

CATEGORY **Spiral Shielded Cables** (See Audio Catalogue)

- A:** Black Soft **PVC** Sheath. Outer Diam. Ø 3,00 (±0,20) mm.
- B:** Shielded with O.F.C. red copper spiral covering 100%.
- C:** Core Insulation with Red PVC – Diam. Ø 1,50 (±0,10) mm.
- D:** O.F.C. red copper formation 8x0,20 mm.
Nom. Cross section 1x0,25 mm².

MARKING
CUSTOM

tasker® C 113 1x0,25 mm² O.F.C. Shielded Cable
 This product is also available in **L.S.Z.H., PE, PUR**, with or without **Steel Armor**.

Cable Properties

Conductor Resistance	75 Ω/Km ± 5%
Capacity Core/Shield	460 pF/mt
Max Rated Voltage	49 V
Operative Temperature	-15/+70°C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego	X	Outdoor Limited	Esterno Limitato	Posa	X	Flexible Limited	Flessibilità limitata	Informazioni	X	Ver. A / 16.12.15
		Outdoor Direct Burial	Esterno Interrato		X	Dynamic (Drag Chain)	Mobile in Catena			
						Dynamic (Torsion)	Mobile in Torsione			