

MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it



Technical Datasheet

tasker® C118 - 2x0,14 mm² - Shielded Flat Audio Cable



A	B	C	D
---	---	---	---

CATEGORY **Shielded Flat Audio Cables** (See Audio Catalogue)

- A:** Soft **PVC** Sheath – Available in different colors.
Outer cable Dimension: 2,90x5,80 (±0,10) mm.
- B:** The single conductors are shielded with O.F.C. red copper spiral covering 100%.
- C:** Core Insulation with PVC, colored one Red and one Yellow.
Diam. Ø: 1,40 (±0,10) mm.
- D:** O.F.C. red copper formation 18x0,10 mm.
Nom. Cross section 2x0,14 mm².

MARKING CUSTOM

tasker® C118 2x0,14 – 26 AWG - O.F.C. Shielded Flat Cable
 This product is also available in **L.S.Z.H., PE, PUR.**

Cable Properties

Conductor Resistance	130 Ω/Km ± 5%
Capacity Core/Core	65 pF/mt
Capacity Core/Shield	280 pF/mt
Max Rated Voltage	49 V
Operative Temperature	-15/+70°C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego	X	Outdoor Limited	Esterno Limitato	Posa	X	Flexible Limited	Flessibilità limitata	Informazioni	X	Ver. B / 16.05.16
		Outdoor Direct Burial	Esterno Interrato		X	Dynamic (Drag Chain)	Mobile in Catena			
				Dynamic (Torsion)	Mobile in Torsione			