



AOC G2 C27G2ZU/BK computer monitor 68.6 cm (27") 1920 x 1080 pixels Full HD LED Black, Red

Brand : AOC

Product family: G2

Product code: C27G2ZU/BK

Product name : C27G2ZU/BK

C27G2ZU/BK - 27" VA display with 240Hz refresh rate, 0.5ms MPRT and 300 nits

AOC G2 C27G2ZU/BK computer monitor 68.6 cm (27") 1920 x 1080 pixels Full HD LED Black, Red:

27" VA display with 240Hz refresh rate, 0.5ms MPRT and 300 nits

240Hz refresh rate, 0.5ms response time and low input lag enable the AOC C27G2ZU to provide a perfectly smooth performance. With its curved design, height adjustment and swivel ability, the monitor can be adjusted to individual needs. It comes with FreeSync Premium and G-Sync compatibility. AOC G2 C27G2ZU/BK. Display diagonal: 68.6 cm (27"), Display resolution: 1920 x 1080 pixels, HD type: Full HD, Display technology: LED, Response time: 0.5 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). Built-in USB hub, USB hub version: 3.2 Gen 1 (3.1 Gen 1). VESA mounting, Height adjustment. Product colour: Black, Red



Display		Ports & interfaces	
Display diagonal *	68.6 cm (27")	HDMI ports quantity	2
Display brightness (typical)	300 cd/m ²	HDMI version	2.0
Display resolution *	1920 x 1080 pixels	DisplayPorts quantity	1
Native aspect ratio *	16:9	DisplayPort version	1.2
Response time	0.5 ms	Audio input	✗
HD type *	Full HD	Headphone out *	✓
Display technology *	LED	Headphone connectivity	3.5 mm
Backlight type	W-LED	Ergonomics	
Screen shape *	Curved	Panel mounting interface	100 x 100 mm
Screen curvature rating	1500R	Cable lock slot *	✗
Screen curvature	150 cm	VESA mounting *	✓
Supported graphics resolutions	1920 x 1080 (HD 1080)	Height adjustment *	✓
Aspect ratio	16:9	Height adjustment	13 cm
Contrast ratio (typical) *	3000:1	Swivelling	✓
Contrast ratio (dynamic)	80000000:1	Swivel angle range	30 - 30°
Maximum refresh rate *	240 Hz	Tilttable	✓
Viewing angle, horizontal	178°	Tilt angle range	3.5 - 21.5°
Viewing angle, vertical	178°	On Screen Display (OSD)	✓
Display number of colours *	16.78 million colours	On Screen Display (OSD) languages	Simplified Chinese, Traditional Chinese, Czech, German, Dutch, English, Spanish, Finnish, French, Italian, Japanese, Korean, Polish, Portuguese, Russian, SER
Panel type *	VA	Number of OSD languages	16
Pixel pitch	0.3114 x 0.3114 mm	Power	
Horizontal scan range	30 - 255 kHz	Energy efficiency class (SDR) *	F
Vertical scan range	48 - 240 Hz	Energy consumption (SDR) per 1000 hours *	24 kWh
Viewable size, horizontal	59.8 cm	Power consumption (typical) *	31 W
Viewable size, vertical	33.6 cm		
Colour depth	8 bit		
sRGB coverage (typical)	120%		
Adobe RGB coverage	89%		

Performance		Power	
AMD FreeSync type	FreeSync Premium	Power consumption (standby) *	0.3 W
NVIDIA G-SYNC *	✗	Power consumption (off)	0.3 W
AMD FreeSync *	✓	AC input voltage	100 - 240 V
AMD FreeSync refresh rate range	48 - 240 Hz	AC input frequency	50/60 Hz
Flicker-free technology	✓	External power adapter	✗
Multimedia		Energy efficiency scale	A to G
Built-in speaker(s) *	✓	Sustainability	
Number of speakers	2	Sustainability certificates	RoHS
RMS rated power	4 W	Weight & dimensions	
Built-in camera *	✗	Width (with stand)	612.4 mm
Design		Depth (with stand)	227.4 mm
Market positioning *	Gaming	Height (with stand)	528.6 mm
Product colour *	Black, Red	Weight (with stand)	5.5 kg
Detachable stand	✓	Width (without stand)	61.2 cm
Heavy metals free	Hg (mercury)	Depth (without stand)	7.32 cm
Certification	CE	Height (without stand)	36.7 cm
Ports & interfaces		Weight (without stand)	4.1 kg
Built-in USB hub *	✓	Packaging data	
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Stand included	✓
USB Type-A downstream ports quantity	4	Cables included	DisplayPort,HDMI
DVI port	✗	Package width	686 mm
HDMI *	✓	Package depth	214 mm
		Package height	523 mm
		Package weight	7.8 kg
		Other features	
		Recyclable packaging material	100%



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.