

MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it

Technical Datasheet



tasker® C4015 – 4x0,15 mm² - Braided Shielded Tinned Cable



CATEGORY Braided Shielded Cable (See General Catalogue)
NOTE The picture don't represent the real number of conductors.

- A:** Grey Soft **PVC** sheath. Outer cable Diam. Ø 4,30 (±0,20) mm.
- B:** Braided Shielding O.F.C. Tinned Copper covering 85%.
- C:** Cores Insulation with Soft **PVC**– DIN 47100 Standards.
 Diam. Ø 1,20 (±0,20) mm.
 Stranded with waste filler between conductors and wrapped with Mylar Tape.
- D:** Stranded O.F.C. Tinned Copper formation 19x0,10 mm.
 Nom. Cross section 4x0,15 mm².

MARKING **tasker®** C 4015 -25 AWG Professional Data Transmission Shielded cable
CUSTOM This product is also available in **L.S.Z.H., PE, PUR**, with or without **Steel Armor**.

Cable Properties

Conductor Resistance	120 Ω/Km ± 5%
Capacity Core/Core	120 pF/mt
Capacity Core/Shield	230 pF/mt
Max Rated Voltage	49 V
Operative Temperature	-15/+70°C

USE	X	Indoor	Interno Edificio	INSTALLATION	X	Fixed	Fissa	INFORMATION	X	RoHS2 Compliant
Impiego		Outdoor Limited	Esterno Limitato	Posa	X	Flexible Limited	Flessibilità limitata	Informazioni	X	Ver. C / 18.07.16
		Outdoor Direct Burial	Esterno Interrato			Dynamic (Drag Chain)	Mobile in Catena			
						Dynamic (Torsion)	Mobile in Torsione			