

MILAN S.r.l. a socio unico

Head Office – Export department:
 Viale Europa, 74
 20090 Cusago (MI) Italy
 T. +39 02 9039.4556-4158
 F. +39 02 9039.4551
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione
 Viale Europa 72 Strada F12
 20090 Cusago (MI) Italy
 T. +39 02 9039.0037-0059
 F. +39 02 9039.0049
 www.tasker.it



Technical Datasheet

tasker® C6025 – 6x0,25 mm² - Braided Shielded Cable



A	B	C	D
---	---	---	---

CATEGORY Braided Conductor Shielded Cable (See Data Network Catalogue)

NOTE The picture don't represent the real number of conductors

- A:** Black Soft **Flame Retardant PVC** Sheath. Outer Diam. Ø 7,00 (±0,20) mm.
- B:** Braided Shielding O.F.C. Red Copper covering 85%.
- C:** Cores Insulation with Soft **Flame Retardant PVC CEI 20-22/II** – DIN 47100 Standards colors – White, Brown, Green, Yellow, Grey and Pink. Nom. Diam. Ø 1,40 mm (±0,10) mm - stranded with waste filler.
- D:** Stranded O.F.C. Red Copper formation 8x0,20 mm. Nom. Cross section 6x0,25 mm².

MARKING tasker® C 6025 6x0,25 mm² O.F.C. SHIELDED CABLE Firestop® Made in Italy

CUSTOM This product is also available in **L.S.Z.H., PE, PUR**, with or without **Steel Armor**.

Cable Properties

Conductor Resistance	75 Ω/Km ± 5%
Capacity Core/Core	130 pF/mt
Capacity Core/Shield	230 pF/mt
Max Rated Voltage	49 V
Operative Temperature	-15/+70°C

USE	X	Indoor	Interno Edificio
Impiego	X	Outdoor Limited	Esterno Limitato
		Outdoor Direct Burial	Esterno Interrato

INSTALLATION	X	Fixed	Fissa
Posa	X	Flexible Limited	Flessibilità limitata
	X	Dynamic (Drag Chain)	Mobile in Catena
		Dynamic (Torsion)	Mobile in Torsione

INFORMATION	X	RoHS2 Compliant
Informazioni	X	Ver. A / 03.11.15