

MILAN S.r.l. a socio unico

Head Office – Export department:  
 Viale Europa, 74  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.4556-4158  
 F. +39 02 9039.4551  
 www.taskercables.com

Ufficio Commerciale e Centro Distribuzione  
 Viale Europa 72 Strada F12  
 20090 Cusago (MI) Italy  
 T. +39 02 9039.0037-0059  
 F. +39 02 9039.0049  
 www.tasker.it

## Technical Datasheet



**Halogen Free**

**Firestop®**

# tasker® C716 U.T.P. 4x2x0,25 mm<sup>2</sup> Cat. 6A 10GBASE-T Ethernet Cable



### ETHERSOUND CATEGORY

Stranded conductors EIA/TIA 568-suitable not only for RJ 45 8 Pin.  
 High Frequency Transmission Data (See Audio Catalogue).

- A:** Grey Soft **L.S.Z.H.** Sheath. Flame Retardant and without halogen.  
Outer cable Diam. Ø 6,70 (±0,20) mm.
- B:** The four pairs are stranded together around a central cross filler in PE and wrapped with polyester based tape.
- C:** Insulation with PE – diam. Ø 1,00 mm - RJ45 plug connector compatible.  
Core colors: White – Blue/Blue White-Orange/ Orange,  
White-Green/Green, White-Brown/Brown.
- D:** Stiff Wire in O.F.C. Red Copper – 1x0,57 mm.  
Nom. Cross section 4x2x0,25 mm<sup>2</sup>.

### MARKING

**tasker®** C716 U.T.P. Cat. 6A 4Px23 AWG SOLID-TYPE CM 60°C L.S.Z.H. (UL)  
 E1888630 CSA LL81295 CMG - ETL Verified TIA/EIA-568-B.2-10 14F2706182621

### CUSTOM

This product is also available in **PVC** polymer, **PE**, **PUR**, with or without **Steel Armor**.

### Cable Properties

<b>Conductor Resistance</b>	75 Ω/Km ± 5%
<b>Impedance</b>	100 Ω± 5%
<b>Max Rated Voltage</b>	49 V
<b>Operative Temperature</b>	-30/+70°C

<b>USE</b>	<input checked="" type="checkbox"/>	Indoor	Interno Edificio	<b>INSTALLATION</b>	<input checked="" type="checkbox"/>	Fixed	Fissa	<b>INFORMATION</b>	<input checked="" type="checkbox"/>	RoHS2 Compliant
<b>Impiego</b>	<input checked="" type="checkbox"/>	Outdoor Limited	Esterno Limitato	<b>Posa</b>	<input checked="" type="checkbox"/>	Flexible Limited	Flessibilità limitata	<b>Informazioni</b>	<input checked="" type="checkbox"/>	Ver. C / 18.07.16
		Outdoor Direct Burial	Esterno Interrato		<input checked="" type="checkbox"/>	Dynamic (Drag Chain)	Mobile in Catena			
						Dynamic (Torsion)	Mobile in Torsione			