



Cordless Heat Gun - Gas powered

CHG900

The HellermannTyton CHG900 Cordless Heat Gun is powered by P445 gas cartridges, providing autonomous working of 90 minutes in one go. The tool is designed to produce flameless heat which makes it the ideal hot-air gun to apply a huge variety of heat shrink tubing and heat shrink wire markers as well as molded shapes or heat shrink boots, transition shapes, end caps and cable repair sleeves especially in harsh outdoor conditions covering freezing temperatures as low as -8 °C.

Features and benefits

- Cordless heat gun powered by P445 gas cartridges
- Flameless heat - no direct flame outlet
- 90 min autonomy per cartridge
- Qualified for harsh outdoor conditions (-8 °C)
- Lightweight 440 g tool (555 g incl. cartridge)
- Hands-free operation due to integrated standing pod
- Quick start piezo ignition
- Instant turnaround due to antiflare feature
- Precise gas flow adjustment
- Ergonomic rugged design
- Quick gas cartridge exchange
- Tool-free maintenance



HellermannTyton Cordless Heat Gun Kit - CHG900.



Gas Nozzle for CHG900 Heat Gun.



Piezo Ignition Trigger for CHG900 Heat Gun.



www.HellermannTyton.co.uk/CHG900-cat22

TYPE	Description	Article-No.
CHG900	Cordless Heat Gun - CHG900 Set incl. P445 Gas Cartridge and 2 nozzles.	391-90010
Piezo CHG900	CHG900 Spare Part - Piezo Ignition Trigger.	391-90011
Gas Nozzle	CHG900 Spare Part - Gas Nozzle.	391-90012
P445	P445 Gas Cartridge (Butane, Propane, Propene).	391-90101

Subject to technical changes.



Add items to your watchlist!

www.HT.click/49-565

