

CLDLWIB 14

Clear Deep Lid Surface Sealed Box



Products may differ in size, colour and appearance to those shown. If you require further information or customisation, please contact us directly.



Material	Polycarbonate, Thermo-resistant ABS
Material sealing gasket	EPDM
Protection class	IP65
Temp. range min	-25 °C
Temp. range max	85 °C
Glow wire test	650 °C
Impact resistance	IK07, IK08
External dimensions LxWxH	380x300x180mm
Type	CLDLWIB 14
Product Color	RAL 7035
Order no. UK	50106966
Packing unit	1

Description:

Surface enclosure
 1/4 turn fast screw system
 Tamper-proof seal

Additional Info:

Double Insulation

Recommended accessories

Backplate 360x280 for Box 380x300	50107218
--	----------

20.08.2019

Your Contact:

WISKA UK Ltd.

Unit 7, Hurling Way · St. Columb Major Business Park · TR9 6SX, St. Columb Major, Cornwall · Great Britain

☎ +44-12-08816062 · 📠 +44-12-08816708

info@wiska.co.uk · www.wiska.co.uk