

CLWIB 4

Clear Lid Surface Sealed Box



Products may differ in size, colour and appearance to those shown. If you require further information or customisation, please contact us directly.



Material	Thermoplastic
Protection class	IP65
Temp. range min	-25 °C
Temp. range max	85 °C
Glow wire test	650 °C
Impact resistance	IK07
External dimensions LxWxH	230x180x88mm
Type	CLWIB 4
Product Color	RAL 7035
Order no. UK	6886LH
Packing unit	1

Description:



1/4 turn plastic screw
without cones
Tamper-proof seal

20.08.2019

Your Contact:

WISKA UK Ltd.

Unit 7, Hurling Way · St. Columb Major Business Park · TR9 6SX, St. Columb Major, Cornwall · Great Britain

 +44-12-08816062 ·  +44-12-08816708

info@wiska.co.uk · www.wiska.co.uk