



AOC G2 CQ32G2SE/BK LED display 80 cm (31.5") 2560 x 1440 pixels 2K Ultra HD Black, Red

Brand : AOC

Product family: G2

Product code: CQ32G2SE/BK

Product name : CQ32G2SE/BK

CQ32G2SE/BK - 31.5" QHD display with 165 Hz, 1 ms response time, FreeSync Premium and 300 nits

[AOC G2 CQ32G2SE/BK LED display 80 cm \(31.5"\) 2560 x 1440 pixels 2K Ultra HD Black, Red:](#)

31.5" QHD display with 165 Hz, 1 ms response time, FreeSync Premium and 300 nits

Its size of 31.5" supports QHD resolution at a refresh rate of 165 Hz and 1 ms response time. Enjoy your favourite games with 1500R curvature and 300-nit luminance. Thanks to FreeSync Premium, display and GPU work in perfect synchronicity.

AOC G2 CQ32G2SE/BK. Display diagonal: 80 cm (31.5"), Display resolution: 2560 x 1440 pixels, HD type: 2K Ultra HD, Display technology: LED, Display surface: Matt, Response time: 1 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in speaker(s). VESA mounting. Product colour: Black, Red



Display		Ports & interfaces	
Display diagonal *	80 cm (31.5")	HDMI ports quantity	2
Display brightness (typical)	250 cd/m ²	HDMI version	2.0
Display resolution *	2560 x 1440 pixels	DisplayPorts quantity	1
Native aspect ratio *	16:9	DisplayPort version	1.2
Response time	1 ms	Audio input	✗
HD type *	2K Ultra HD	Headphone out *	✓
Display technology *	LED	Headphone outputs	1
Backlight type	W-LED	Headphone connectivity	3.5 mm
Display surface	Matt	DC-in jack	✓
Screen shape *	Curved	Ergonomics	
Screen curvature rating	1500R	Panel mounting interface	100 x 100 mm
Screen curvature	150 cm	Cable lock slot *	✓
Supported graphics resolutions	2560 x 1440	Cable lock slot type	Kensington
Supported video modes	1080p,1440p	VESA mounting *	✓
Aspect ratio	4:3,16:9	Height adjustment *	✗
Contrast ratio (typical) *	3000:1	Tilttable	✓
Contrast ratio (dynamic)	80000000:1	Tilt angle range	-3.5 - 21.5°
Maximum refresh rate *	165 Hz	On Screen Display (OSD)	✓
Viewing angle, horizontal	178°	On Screen Display (OSD) languages	Simplified Chinese, Traditional Chinese, Czech, German, Dutch, English, Spanish, Finnish, French, Italian, Japanese, Korean, Polish, Portuguese, Russian, SER
Viewing angle, vertical	178°	Number of OSD languages	16
Display number of colours *	16.78 million colours	Plug and Play	✓
Panel type *	VA	Power	
Pixel pitch	0.2724 x 0.2724 mm	Energy efficiency class (SDR) *	G
Viewable size, horizontal	69.7 cm	Energy consumption (SDR) per 1000 hours *	35 kWh
Viewable size, vertical	39.2 cm		
Colour depth	8 bit		
RGB colour space	sRGB		
sRGB coverage (typical)	121%		
NTSC coverage (typical)	85%		

Display		Power	
Adobe RGB coverage	90%	Power consumption (typical) *	49 W
Performance		Power consumption (standby) *	0.3 W
AMD FreeSync type	FreeSync Premium	Power consumption (off)	0.3 W
NVIDIA G-SYNC *	✗	AC input voltage	100 - 240 V
AMD FreeSync *	✓	AC input frequency	50/60 Hz
AMD FreeSync refresh rate range	48 - 165 Hz	External power adapter	✓
Flicker-free technology	✓	Energy efficiency scale	A to G
Low Blue Light technology	✓	Sustainability	
Multimedia		Sustainability certificates	RoHS, ENERGY STAR
Built-in speaker(s) *	✓	Weight & dimensions	
Number of speakers	2	Width (with stand)	709.9 mm
RMS rated power	5 W	Depth (with stand)	244.9 mm
Built-in camera *	✗	Height (with stand)	524.4 mm
Design		Weight (with stand)	7.4 kg
Market positioning *	Gaming	Width (without stand)	71 mm
Product colour *	Black, Red	Depth (without stand)	8.72 cm
Frameless design	✓	Height (without stand)	42.6 cm
Front bezel colour	Black	Weight (without stand)	7.5 kg
Detachable stand	✓	Packaging data	
Feet colour	Black	Stand included	✓
Heavy metals free	Hg (mercury)	Cables included	AC, DisplayPort, HDMI
Certification	ISO	DisplayPort cable length	1.8 m
Ports & interfaces		HDMI cable length	1.8 m
Built-in USB hub *	✗	Package width	813 mm
DVI port	✗	Package depth	225 mm
HDMI *	✓	Package height	607 mm
		Package weight	10.5 kg
		Package type	Box
		Other features	
		Recyclable packaging material	100%



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.