



CT 10 TS

E1621600

CABLE CUTTER 1-HANDED WITH STRIPPING BLADE 0.2-25mm², MAX D=8mm. RETURN SPRING

Cable cutter with return spring and double jaws. Cuts and strips copper and aluminium cable. Forged steel with polished / hardened jaws. Multi colors soft grip handles available.

Cutting capacity. Max YD: 8mm Stranded cable: 25mm² Solid Cable: 16mm²

Length: 122mm

Product Properties:

Insulated	Yes
Suitable for solid cores	Yes
Suitable for stranded conductors	Yes
Suitable for fine strand conductors	Yes
Grip design	1-component
With impact protection	No
Suitable for steel wire braiding	No
Replaceable cutting head	No
Cutting jaws exchangeable	No
With strip function	Yes
Construction/operation	Mechanic one hand
Isolation protection 1000 V	No
With spring	Yes

Dimensions:

Unit	pcs
Max. cable cross section	0.5-25 mm ²
Suitable for max. cable diameter	8 mm

Total length	122 mm
MOQ	1 .

Approvals:

VDE tested	No
Isolation protection 1000 V	No

Compliance:

RoHS	RoHS 3 (2015/863)
Conflict minerals	N/A, Contains no conflict minerals
Reach	No SVHC (223 Subs. Jan 2022)

Other information:

Trademark	NEMIQ
ETIM-Class	EC000142 - Cable shears
ETIM-Release	7.0
Product Group	1-hand
Search Description	CCTOOLS
Alternative SKU	CT10TS

Logistic information:

Barcode	733117635324
E-no	E1621600
Country of origin	JP
Item status	Stock item, normally in stock with reservation for in between sales.
Stock code	CT 10 TS
Taric code	82032000
Unit	pcs
MOQ	1 .