

Juniper CTP-SFP-1GE-T Compatible SFP Module - 1000BASE-T - SFP to RJ45 Cat6/Cat5e - 1GE Gigabit Ethernet SFP - RJ-45 100m

Product ID: CTPSFP1GETST



The CTPSFP1GETST is a Juniper CTP-SFP-1GE-T compatible copper transceiver module that has been designed, programmed and tested to work with Juniper brand switches and routers. It delivers dependable 1 GbE connectivity over copper cable, for 1000Base-T compliant networks, with a maximum distance of up to 100 m (328 ft).

Technical Specifications:

- Maximum Data Transfer Rate: 1000 Mbps (1 Gbps)
- Type: Copper
- Connection Type: RJ-45
- Maximum Transfer Distance: 100 m (328 ft)
- MTBF: 4,655,371 hours
- Power Consumption: Low power consumption
- Digital Diagnostics Monitoring (DDM): Yes

This SFP copper module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility

Applications

Features

- **100% JUNIPER CTP-SFP-1GE-T COMPATIBLE SFP TRANSCEIVER:** Designed, programmed and tested to work with compatible Juniper switches and routers to deliver dependable 1GbE connectivity
- **TECHNICAL SPECS:** 1000BASE-T 1Gbps Copper RJ-45 Connector Distances up to 100m (328ft)
- **TESTED FOR OEM HOST COMPATIBILITY:** Hot-swappable in Juniper routers and switches
- **LIFETIME WARRANTY:** Backed by a lifetime warranty on the life of the module itself - not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24.
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

Hardware

| | |
|--------------------|-----------------------|
| Warranty | Lifetime |
| Compatible Brand | Juniper |
| Industry Standards | IEEE 802.3 1000BASE-T |

Performance

| | |
|----------------------------|--------------------|
| Maximum Data Transfer Rate | 1.00 Gbps |
| Max Transfer Distance | 100 m (328 ft) |
| Type | Copper |
| Fiber Operating Mode | Full-Duplex |
| DDM | Yes |
| Compatible Networks | 1000 Mbps (1 Gbps) |
| MTBF | 4,655,371 hours |

Connector(s)

| | |
|-------------|----------|
| Connector A | SFP Slot |
| Connector B | RJ-45 |

Physical



Characteristics

| | |
|-------------------|------------------|
| Product Length | 2.6 in [65.0 mm] |
| Product Width | 0.6 in [14.0 mm] |
| Product Height | 0.5 in [12.0 mm] |
| Weight of Product | 2.5 oz [72.0 g] |

Packaging Information

| | |
|---------------------------|------------------|
| Package Length | 9.1 in [23.0 cm] |
| Package Width | 8.1 in [20.7 cm] |
| Package Height | 0.6 in [15.0 mm] |
| Shipping (Package) Weight | 2.8 oz [80.0 g] |

What's in the Box

| | |
|---------------------|-----------------|
| Included in Package | SFP Transceiver |
|---------------------|-----------------|

**Product appearance and specifications are subject to change without notice.*

