Drawing No.	Rev.	Page
CWA6S-24-CD-W18	Е	1 / 2

SPECIFICATIONS

	CWA6S-24-CD		
	CD		
	Daylight		
.)	6500 K		
m)	220lx		
VDC)	770lm		
	24V DC (Polarized)		
ge	Rated Voltage ±10%		
Тур.	360mA		
Max.	396mA		
ature	-30 °C to +60 °C		
dity	Less than 90% (No condensation)		
ature	-35 °C to +65 °C		
ity	Less than 90% (No condensation)		
	All Directions		
Protection Rating	IP65 (IEC 60529)		
	(Cable connection ends not included)		
Vibration Resistance	19.6 m/s ²		
	(30Hz, Back and Forth, Up and Down, Left and Right for 2 hrs. each)		
Mass 370±15g			
	Refer to the Outer Dimension Drawing		
Conformity Standards	EMC Directive (EN 55015, EN 61000-6-2)		
	RoHS Directive (EN IEC 63000)		
	UL Listed (File No.E306141)		
Remarks • Due to the inherent properties of the LED, color variations and hue may occur			
	m) J DC) ge Typ. Max. ature dity ature ity		

