Drawing No.	Rev.	Page
CWA9S-24-CD-W18	Е	1 / 2

SPECIFICATIONS

[General Specifications]				
Model		CWA9S-24-CD		
Color Code		CD		
Luminous Color		Daylight		
Color Temperature (typ.)		6500 K		
Illuminance (at 24V DC,1m)		330lx		
Total Luminous Flux (at 24V DC)		1155lm		
Rated Voltage		24V DC (Polarized)		
Operating Voltage Range		Rated Voltage ±10%		
Signal Wire Current	Тур.	540mA		
(Rated Current Consumption)	Max.	594mA		
Operating Ambient Temperature		-30 °C to +60 °C		
Operating Ambient Humidity		Less than 90% (No condensation)		
Storage Ambient Temperature		-35 °C to +65 °C		
Storage Ambient Humidity		Less than 90% (No condensation)		
Mounting Direction		All Directions		
Protection Rating		IP65 (IEC 60529)		
		(Cable connection ends not included)		
Vibration Resistance		19.6 m/s ²		
		(30Hz, Back and Forth, Up and Down, Left and Right for 2 hrs. each)		
Mass		530±25g		
Outer Dimensions		Refer to the Outer Dimension Drawing		
Conformity Standards		EMC Directive (EN 55015, EN 61000-6-2)		
		RoHS Directive (EN IEC 63000)		
		UL Listed (File No.E306141)		
Remarks		· Due to the inherent properties of the LED, color variations and hue may occur.		

