CanoScan LiDE 400 SUPERIOR SCANNER WITH EXCEPTIONAL SPEED, QUALITY AND STYLE

A premium scanner with enhanced speed and a high-resolution scanning capability to save space, power and time. Its sophisticated design features a compact, upright stand and easy USB Type-C powered connection.







- Sharp, high-speed A4 scanning in just 8 seconds
- · Stylish, lightweight design with convenient vertical stand
- · Easily scan thick documents with advanced Z-Lid
- Powered simply by single USB Type-C cable
- Instant scanning with 5 EZ one-touch operation buttons







48-bit





PRODUCT RANGE



CanoScan LiDE 300

CanoScan LiDE 300



CanoScan LiDE 400

CanoScan LiDE 400



TECHNICAL **SPECIFICATIONS**

CanoScan LiDE 400

Туре Flatbed Scanner

Scanning element 3-color (RGB) LED Light source Optical resolution 4800 x 4800dpi [1] 25 - 19200dpi ^[4] Selectable resolution

USB-Type C (USB 3.0 and 2.0 compatible)

Scanning gradation (colour) 48 bit input -> 48/24 bit output Scanning gradation 16 bit input -> 8 bit output (greyscale)

Maximum document size A4 / Letter (216 x 297mm)

EZ-Scan Buttons 5 buttons (PDF x 2, AUTOSCAN, COPY, SEND)

Scanning speed (colour) (Reflective) 25.4msec/line (4800 dpi) 14.8msec/line (2400 dpi) 6.6msec/line (1200 dpi)

3.8msec/line (600 dpi) 1.7msec/line (300 dpi) [2] Scanning speed (greyscale, B&W) 8.2msec/line (4800 dpi) 4.3msec/line (2400 dpi) 2.2msec/line (1200 dpi) 1.3msec/line (600 dpi) (Reflective)

1.7msec/line (300 dpi) [2] Scan speed (A4, 300dpi, Approx. 8 sec [3]

Approx. 4 sec [3] Scan speed (4x6", 300dpi,

Preview Speed Approx. 7 sec [5] Scan Gear for Win Scan Utility for Win Software included Supplied via USB port

approx. 4.5W (in operation, maximum) Power consumption

approx. 0.3W (standby) Dimensions 250 x 365 x 39 mm

Weight Operating range 5 - 35 °C

Operating range (humidity)

10 - 90 %RH, without condensation formation Windows 10, Windows 8.1, Windows 7 SP1 [6] [7 Supported Operating Systems Operation can only be guaranteed on a PC with

pre-installed Windows 7 or later OS X 10.11.6, macOS 10.12~macOS 10.13

Minimum System Display: 1024 x 768 XGA

Requirements

Power supply

Standard disclaimers

All Specifications subject to change without notice.

All brand and product names are trademarks of their respective companies.

Footnotes

- $Optical\ resolution\ is\ a\ measure\ of\ maximum\ hardware\ sampling\ resolution,\ based\ on$ ISO 14473 standard.
- The fastest speed in Hi-Speed USB on Windows PC. Transfer time to computer is not
- included.

 Connecting the bundled USB cable to the port corresponding to USB3.0 and above on PC. Color document scan speed: (Color A4 300dpi) is measured with ISO/IEC 29183 Target-A. Color photo scan speed: (4"x6" 300dpi) is measured with ISO//JIS SCID No.2. Scan speed indicates the time measured between pressing the scan button of the scanner driver and the on-screen status display turns off. Scan speed may vary depending on system configuration, interface, software, scan mode settings and document size etc.
- Increasing the scanning resolution will limit the maximum possible scanning area.
- Preprocessing time is not included.
- Internet connection or CD-ROM drive is required to install the software for Windows. Internet connection is required to use all the user's guide.
- TWAIN driver (ScanGear) is based on the TWAIN specification V1.9 and requires the Data Source Manager comes with the operating system.

Canon Inc. canon.com Canon Europe canon-europe.com English edition Canon Europa NV 2018



SUPERIOR SCANNER WITH EXCEPTIONAL SPEED, QUALITY AND STYLE

CanoScan LiDE 400

A premium scanner with enhanced speed and a high-resolution scanning capability to save space, power and time. Its sophisticated design features a compact, upright stand and easy USB Type-C powered connection.

Sales Start Date: September 2018



PRODUCT DETAILS:

| Product Name | Mercury Code | EAN Code | Recommended Retail Price | |
|-------------------|--------------|---------------|--|--|
| CanoScan LiDE 400 | 2996C010AA | 4549292119855 | <please fill="" in="" rrp=""></please> | |

MEASUREMENT / LOGISTIC INFORMATION:

| Product Name | Mercury Code | Pack type | Pack description | Quantity per pack | Length (mm) | Width (mm) | Height (mm) | Gross Weight (kg) |
|-------------------|--------------|--------------|------------------|----------------------|----------------|---------------|----------------|----------------------|
| CanoScan LiDE 400 | 2996C010AA | EA | Individual | 1 | 432.5 | 91.5 | 317.5 | TBC |
| | | СТ | Pallet (Upper) | 72 | 876 | 1,109 | 965 | TBC |
| | | EP | Pallet (Bottom) | 96 | 876 | 1,109 | 1,285 | TBC |

What's in the box?

- A4 flatbed scanner CanoScan LiDE 400
- USB cable
- Manuals and other documents
- Vertical stand

