QUICK AND EASY PORTABLE DOCUMENT SCANNER

SIMPLY CONNECT AND SCAN ANYWHERE, ANYTIME!







Compact design

Take the R10 scanner with you on the go. A sleek, lightweight device, it's conveniently sized for portable use – the ideal companion for home offices, classrooms, remote workspaces and everywhere in between

• Easy to use

Simply connect and scan in a matter of seconds without the need to install any driver or software applications, using Canon's unique embedded CaptureOnTouch Lite software

Efficient single pass scanning

Scan double-sided documents in one smooth motion at a speed of 12ppm, with the added efficiency of a 20-sheet feeder capacity, helping you streamline your workflow on the go

Speedy USB-powered scanner

Never worry about forgetting chargers, with a device that works with a USB cable only, minimizing hassle and reducing the time it takes to start scanning

Intuitive paper handling

Reliably scan a range of documents from A4 papers to receipts and plastic business cards. Advanced document detection features automatically adjust scan settings, so you can achieve optimal results with every scan

Environmentally friendly

Eco-friendly packaging with energy saving ultra-low power consumption

PRODUCT RANGE



imageFORMULA R40



TECHNICAL SPECIFICATIONS



GENERAL PRODUCT INFORMATION

USB Powered A4 Sheetfed Portable Scanner Туре

Scanning sensor unit CMOS CIS 1 Line Sensor

Optical resolution 600dpi Light source RGB LED

Scanning side Front / Back / Duplex

Interface USB 2.0

Tray Closed :285 (W) x 95 (D) x 40 (H)mm Tray Opened: 285 (W) x 257 (D) x 174 (H)mm Dimensions (WxDxH)

Weight Approx. 0.9kg

Power requirements USB 2.0 bus power: 0.5A

2.5W or less (Energy Saving Mode: 1.5W) Power consumption

Temperature: 10°C to 32.5°C Humidity: 25% to 80% RH Operating environment

SCANNING SPECIFICATIONS

Black and White 12 pages per min. / 14 images per min. Colour 9 pages per min. / 10 images per min. Output resolution 150 / 200 / 300 / 400 / 600dpi Output mode Colour, Grayscale, Black and White

Suggested Daily Duty Cycle Approx. 500 scans

DOCUMENT SPECIFICATIONS

Width 50.8 - 216mm Length 70 - 356mm

Thickness 64 - 128g/m² (0.08 - 0.15mm)

Business card scanning Width: 49mm

Length: 85mm Thickness: 128-225g/ m² (0.15 - 0.3 mm)

Plastic card scanning

Width: 54mm Length: 86mm Thickness: Less than 1.4mm (Embossed card can be scanned) Paper separation Separation Pad Method

20-sheets Feeder capacity

OTHER FEATURES

Page Size Detection, Auto Resolution Setting, Background Smoothing, Character Emphasis, Color Dropout / Enhance Color, Deskew, Double-Feed Detection, Edge Emphasis, Image Rotation, Moiré Reduction, Pre-Scan, Prevent Bleed-Through/Remove Background, Skip Blank Page, Text Enhancement, Text Orientation Recognition,

BUNDLED SOFTWARE

Windows

Built-in CaptureOnTouch Lite Scanning software (Windows 8.1 / 10 - 32bit/64bit)

Built-in CaptureOnTouch Lite Scanning software (macOS 10.12 / 10.13 / 10.14 / 10.15)

CONSUMABLES Separation Pad, Feed Roller

ACCESSORIES USB Cable

Disclaimer

All data is based on Canon standard testing methods except where indicated. Subject to change without notice.

Canon Ireland 3006 Lake Drive Citywest, Saggart Co. Dublin, Ireland Telephone No: 01 2052400 Facsimile No: 01 2052525

canon.ie

Uxbridge UB11 1ET www.canon.co.uk

Tel: 01895 648 000

Canon (UK) Ltd

5 The Square

Stockley Park

Canon Electronics Inc. canon-elec.co.jp

Canon Europe canon-europe.com **English** edition © Canon Europa N.V.,2021

