SIMPLE & RELIABLE **DESKTOP SCANNER**



Easy to use

Enjoy quick and easy scanning, with an intuitive user interface that lets you scan, edit and finalise at the touch of a button, plus create up to 9 routine jobs for added ease and efficiency

Easy installation and set up

Install your scanner in just a few simple steps with an integrated allin-one installer. Automatic software update function ensures your CaptureOnTouch application and Canon drivers are always up to date to ensure quality and reliability at all times

Accurate and Consistent

Scan a batch of mixed documents of any shape and size in one easy process with Canon's reliable 60-sheet feeder, capable of scanning everything from standard A4 documents to thick and thin papers like ID cards, receipts, post cards and documents up to 3m long

Maximise productivity

Save time with fast double-sided scanning of up to 40 pages per minute. Advanced image processing features such as auto size detection, document de-skew, text orientation and colour detection mean there's no need to sort documents or frequently change settings while scanning

Effortless productivity in your home or small office environment





Scan to cloud

Simple one touch scanning of various documents types, converting them into useful formats for editing, or simply for you to upload to your favorite cloud application

 Superior quality and design
 A stylish, ultra-compact desktop device that delivers consistently superior image quality. Capture fine details with advanced text enhancement,
producing sharp copies with greater readability, ideal for documents with faint light text or patterned backgrounds

Cut your overheads and reduce your environmental impact in one. Canon's imageFORMULA series offers impressively low power consumption, using just 19W or less when in operation and 1.4W or less in sleep mode

PRODUCT RANGE



imageFORMULA R10



TECHNICAL SPECIFICATIONS



GENERAL PRODUCT INFORMATION

Desktop Type Sheet Fed Scanner Туре

CMOS CIS 1 Line Sensor Scanning sensor unit

Optical resolution 600dpi RGB LED Light source

Scanning side Front / Back / Duplex

Interface USB 2.0

Trays Closed: 291 x 250 x 245 mm Trays Opened: 291 x 600 x 382 mm Dimensions (WxDxH)

Weight Approx. 2.8kg

AC 100-240V (50/60Hz) Power requirements Scanning: 22W or less Sleep mode: 1.4W or less Power turned off: 0.1W or less Power consumption

Operating environment

SCANNING SPECIFICATIONS

Black and White

Colour 30 pages per min. / 60 images per min. Detect Automatically, 100/150 / 200/240/300/400/600 dpi Output resolution

Detect Automatically, Black and White, Error Diffusion, Advanced Text Enhancement, Advanced Text Ehancement II, 256-level gray, 24-bit Colour Output mode

40 pages per min. / 80 images per min.

Suggested Daily Duty Cycle Approx. 4000 scans

DOCUMENT SPECIFICATIONS

Width 50.8 - 216mm Length 54 - 356mm

20 - 209g/m² (0.04 - 0.25mm) Thickness

Long document mode Up to 3000mm

Business card scanning Size: 50 x 85mm or larger Thickness: Less than 0.45 mm

Plastic card scanning

Size: 54 x 86mm Thickness: Less than 1.4mm (Embossed Card is supported)

Paper separation Retard Roller Method Feeder capacity 60 Sheets (80g/m²)

OTHER FEATURES

Auto Colour Detection, Auto Page Size Detection, Auto Resolution Setting, Background Smoothing, Batch Separation, Character Emphasis, Colour Dropout / Enhance Colour, Deskew, Double-Feed Detection, Edge Emphasis, Folio Scan, Image Rotation, Moire Reduction, MultiStream, Pre-Scan, Prevent Bleed-Through/Remove Background, Skip Blank Page, Text Enhancement, Text Orientation Recognition, Three-Dimensional Colour Correction, Ultrasonic Double-Feed Detection, User Preferences

BUNDLED SOFTWARE

TWAIN Driver (Windows 7 SP1 / 8.1 / 10 - 32bit/64bit), Canon CaptureOnTouch Scanning Software, Readiris PDF Software, Cardiris Business Card Software Windows

TWAIN Driver (macOS 10.12 / 10.13/10.14/10.15), CaptureOnTouch Scanning Software

Consumables Exchange Roller Kit

Disclaime

Canon Ireland 3006 Lake Drive Citywest, Saggart Co. Dublin, Ireland Telephone No: 01 2052400 Facsimile No: 01 2052525

canon.ie

Canon (UK) Ltd 5 The Square Stockley Park Tel: 01895 648 000

Canon Europe Uxbridge canon-europe.com UB11 1ET **English** edition © Canon Europa N.V.,2021 www.canon.co.uk

Canon Electronics Inc.

canon-elec.co.jp

