

CHERRY STREAM 3.0





Models may vary from the image shown

The workhorse for continuous use

CHERRY STREAM 3.0 never stops working. Specially developed for continuous use in the office: Abrasion-resistant inscription of keys, whisper keystroke, splash water-protected and ultra-flat, ergonomic design.

Key benefits

- Durable abrasion-resistant inscription of key caps
- Designed for continuous usage over 20 mill. confirmations per key
- Spill resistant
- Plug & Play for easy commissioning with no software installation
- Ultra-flat ergonomic top-design for fatigue-free work
- Ultra silent. Whisper keystroke for low-noise typing
- 6 HotKeys for comfortable volume control and the most important Mediaplayer functions
- Standard keyboard layout (including cursor and number block)
- Blue status LEDs
- GS approval
- Awarded the "Blaue Engel" environmental seal

Technical Data:

Layout (country or language):

Product dependant, see table "Models"

Housing colour:

Product dependant, see table "Models"

Key colour:

Product dependant, see table "Models"

Weight (product):

approx. 936 g

Total weight (with packaging):

approx. 1205 g

Cable Length:

approx. 1.80 m

Storage Temperature:

-20°C to 65°C

Operating Temperature:

0°C to 40°C

Current Consumption:

max. 25 mA

Interface:

• USB

Product approvals:

cURus

VDE GS

c-tick

VCCI

• CE • FCC

c**71**0s







F©

System requirements:

USB connection

Delivery Volume:

- CHERRY STREAM 3.0
- Operating instructions in hard copy

Dimensions (product):

approx. 472 x 176 x 18 mm

Packaging dimensions:

approx. 485 x 220 x 30 mm

Reliability:

• MTBF > 80,000 hours

Keyboard:

- Key technology: SX
- Service life, standard key: > 20 million key operations
- Inscription technology: Laser
- Inscription layout: Product dependant, see table "Models"
- Number of Keys: Product dependant, see table "Models"

Packaging Unit:

- Number of products in the master package: 6
- Number of master packages per pallet: 28

Warranty:

3-year limited manufacturer's guarantee

For the first two years after delivery, the statutory warranty applies. In the third year after delivery, CHERRY voluntarily grants an additional warranty according to the following conditions ("extended warranty"). In the event of a defect, please contact the seller of your CHERRY product. Do not carry out any repairs on your own and do not open the product. There is no warranty if unauthorized changes to the product cause a defect.



Conditions for the extended warranty:

In the case of a defect after the first 2 years after delivery of the CHERRY product, CHERRY grants its customers for the additional period of one year the right to assert claims for cure, i.e. demand that the defect is remedied or a thing free of defects is supplied. The extended warranty is to be asserted against the seller of the CHERRY product upon presentation of the original invoice, proof of purchase or a comparable proof of the time of purchase.

CHERRY, and the seller of the CHERRY product, where applicable, shall remedy the defect in the event the customer has justified claims for cure under the terms of the extended warranty.

Excluded from the extended warranty are damages caused by improper use, in particular by the effects of chemical substances, other damages caused by external influences, as well as normal wear and tear and optical changes, in particular discoloration or abrasion of shiny areas. Also excluded from the extended warranty are accessories and other parts which are not an integral part of the purchased item.

Errors, technical changes and delivery possibilities excepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.



Models:

(possible country/layout versions, others available on request)

	Product name	Order number	EAN code	Layout (country or		Key colour	Inscription layout	
				language)	colour			Keys
1	CHERRY STREAM 3.0	G85-23200BE-0	4025112083150	Belgium	pale grey	pale grey	Standard	105+6
2	CHERRY STREAM 3.0	G85-23200BE-2	4025112083273	Belgium	black	black	Standard	105+6
3	CHERRY STREAM 3.0	G85-23200CH-0	4025112083235	Switzerland	pale grey	pale grey	Standard	105+6
4	CHERRY STREAM 3.0	G85-23200CH-2	4025112083174	Switzerland	black	black	Standard	105+6
5	CHERRY STREAM 3.0	G85-23200CS-0	4025112085840	Czech Republic / Slovakia	pale grey	pale grey	Standard	105+6
6	CHERRY STREAM 3.0	G85-23200CS-2	4025112085857	Czech Republic / Slovakia	black	black	Standard	105+6
7	CHERRY STREAM 3.0	G85-23200DE-0	4025112083242	Germany	pale grey	pale grey	Standard	105+6
8	CHERRY STREAM 3.0	G85-23200DE-2	4025112083181	Germany	black	black	Standard	105+6
9	CHERRY STREAM 3.0	G85-23200DEADSP	4025112085055	Germany (EUROPA 2 DIN2137)	black	black	DIN 2137-T2	105+6
10	CHERRY STREAM 3.0	G85-23200DEAESP	4025112085062	Germany (EUROPA 2 DIN2137)	pale grey	pale grey	DIN 2137-T2	105+6
11	CHERRY STREAM 3.0	G85-23200ES-0	4025112086052	Spain	pale grey	pale grey	Standard	105+6
12	CHERRY STREAM 3.0	G85-23200ES-2	4025112085291	Spain	black	black	Standard	105+6
13	CHERRY STREAM 3.0	G85-23200EU-0	4025112083259	US English with EURO symbol	pale grey	pale grey	Standard	104+6
14	CHERRY STREAM 3.0	G85-23200EU-2	4025112083198	US English with EURO symbol	black	black	Standard	104+6
15	CHERRY STREAM 3.0	G85-23200FR-0	4025112083266	France	pale grey	pale grey	Standard	105+6
16	CHERRY STREAM 3.0	G85-23200FR-2	4025112083204	France	black	black	Standard	105+6
17	CHERRY STREAM 3.0	G85-23200GB-0	4025112083167	UK	pale grey	pale grey	Standard	105+6
18	CHERRY STREAM 3.0	G85-23200GB-2	4025112083211	UK	black	black	Standard	105+6
19	CHERRY STREAM 3.0	G85-23200HU-0	4025112086090	Hungary	pale grey	pale grey	Standard	105+6
20	CHERRY STREAM 3.0	G85-23200IT-0	4025112086069	Italy	pale grey	pale grey	Standard	105+6
21	CHERRY STREAM 3.0	G85-23200IT-2	4025112085307	Italy	black	black	Standard	105+6
22	CHERRY STREAM 3.0	G85-23200PN-0	4025112083143	Pan-Nordic	pale grey	pale grey	Standard	105+6



	Product name	Order number	EAN code	Layout (country or	Housing	Key colour	Inscription layout	Number of
				language)	colour			Keys
23	CHERRY STREAM 3.0	G85-23200PN-2	4025112083228	Pan-Nordic	black	black	Standard	105+6