CHERRY MW 2310 2.0

Wireless Mouse





Models may vary from the image shown

Wireless freedom – battery life of up to 3 years

The CHERRY MW 2310 2.0 is a versatile 6-button wireless mouse with 2.4 GHz technology and an ergonomic design.

Its nano USB receiver is so small that it can safely stay inside the notebook even when you're on the move – the mouse is always ready for use.

The CHERRY MW 2310 2.0 has an optical sensor with 3 adjustable resolutions (1000/1600/2400 DPI). Using the DPI switch on the top of the mouse, the resolution can be selected at the touch of a button. An LED indicates the selected DPI.

The technical concept makes the successor to the legendary CHERRY MW 2310 especially energy-efficient. With just one set of the supplied batteries (2 x AA), the mouse can be operated for up to 3 years before they have to be changed. The mouse has an On/Off switch on the bottom so it can be switched off completely when not in use.

Advanced materials, a comfortable feel and great versatility make the CHERRY MW 2310 2.0 what it is – the CHERRY mouse for superior performance at a surprisingly low price.

Key Benefits

- 6-button mouse: Optical sensor and adjustable resolution (1000/1600/2400 dpi)
- Nano USB receiver: can stay plugged into in the notebook permanently
- Long battery lifespan thanks to energy-efficient infrared sensor
- Optimized for both left-handed and right-handed operation
- Elegant touch due to the chrome plated scroll wheel with nonslip rubber coating
- Easy to install, requiring no technical knowledge
- Interference-free, wireless 2.4 GHz technology (with a range of approx. 10 m)

Technical Data

Weight (product)

approx. 122 g (mouse with battery), approx. 2 g (receiver)

Total weight (with packaging)

approx. 158 g

Transmission range

approx. 10 m

Frequency range

2.400 GHz - 2.4835 GHz

Storage Temperature

-20 °C to 55 °C

Operating Temperature

0 °C to 40 °C

Current Consumption

Mouse: typ. 7 mA, Receiver: typ. 26 mA

Interface

USB

Product approvals

CE



cTUVus

F

FCC

System requirements

USB connection

Delivery Volume

- CHERRY MW 2310 2.0
- 2 batteries (type AA)
- Operating instructions
- 1 nano USB transmission receiver



CHERRY MW 2310 2.0

Wireless Mouse

Dimensions (product)

119,96 x 75,52 x 38,32 mm (Mouse) 18 x 13,1 x 5,7 mm (Receiver)

Packaging dimensions

130 x 94 x 50 mm

Mouse

Scanning: optical

Resolution: 1000/1600/2400 dpi (adjustable)

Number of Keys: 6

Mouse wheel design: Scroll wheel with key function

Design: SymmetricalConnection: wirelessHousing colour: blackKey colour: black

Packaging Unit

Number of products in the master package: 10

• Number of master packages per pallet: 108

Errors, technical changes and delivery possibilities excepted. Technical information refers only to the specifications of the products. Features may differ from the information provided.

Warranty

We put a lot of dedication and hard work into the development of our products and we are proud of their quality. This is why, in addition to the statutory guarantee mentioned in the operating instructions, we are granting an expanded manufacturer's guarantee that is subject to the conditions stated below. For the first two years after delivery, the statutory warranty applies. In the third year after delivery, CHERRY voluntarily grants an additional warranty according to the following conditions ("extended warranty"). In the event of a defect, please contact the seller of your CHERRY product. Do not carry out any repairs on your own and do not open the product. There is no warranty if unauthorized changes to the product cause a defect.

Conditions for the extended warranty

In the case of a defect after the first 2 years after delivery of the CHERRY product, CHERRY grants its customers for the additional period of one year the right to assert claims for cure, i.e. demand that the defect is remedied or a thing free of defects is supplied. The extended warranty is to be asserted against the seller of the CHERRY product upon presentation of the original invoice, proof of purchase or a comparable proof of the time of purchase. CHERRY, and the seller of the CHERRY product, where applicable, shall remedy the defect in the event the customer has justified claims for cure under the terms of the extended warranty. Excluded from the extended warranty are damages caused by improper use, in particular by the effects of chemical substances, other damages caused by external influences, as well as normal wear and tear and optical changes, in particular discoloration or abrasion of shiny areas. Also excluded from the extended warranty are accessories and other parts which are not an integral part of the purchased item.

Models

	Product name	Order number	EAN-Code
1	CHERRY MW 2310 2.0	JW-T0320	4025112089978