



11 Pc. Pass-Thru™ X6™ Black Oxide Adjustable Wrench & Socket Set

Product Details

Catalog No.	CPTAW8
UPC	037103283559
SAE/Metric/Torx	SAE/Metric/Torx®
Set Piece Count	11
Finish	Black Phosphate
Handle Material	Alloy Steel
Set Size Range Min	3/8 (10mm)
Set Size Range Max	3/4 (19mm)
Set Included Storage	Plastic Tray
Height	40 mm
Width	102 mm
Jaw Size Scale	Yes
Weight (Catalog)	0,992 kg
Jaw Opening/Capacity	25,4 mm
End B Ratcheting Type	Reversing
End A SAE/MET	SAE/MET
Packaging	Peg Hook/Retail Packaging



Features

- Versatile Fastening Tool Offers User Multiple Fastening Options in a Single Tool Design
- Traditional 8" Adjustable Wrench with Laser Etched SAE/MM Scales and Wide Jaw Opening
- Pass-Thru Reversible Ratcheting System Works Over Long Threaded Rod Where Normal Ratchets and Sockets Won't Fit
- Every Pass-Thru Socket Replaces One Standard and One Deep
- Universal Design Fits 6 Fastener Types (Hex, Square, 12pt, E-Torx, Partially Rounded Hex, Spline)
- Includes 10 Universal Combo Sockets that Fit Both Standard and Metric Fasteners: 3/8" (10mm), 7/16" (11mm), 15/32" (12mm), 1/2" (13mm), 9/16" (14mm), 19/32" (15mm), 5/8" (16mm), 11/16" (17mm), 23/32" (18mm), 3/4" (19mm)
- Sockets are Clearly Marked for Easy Identification
- For Pipe Work, the Jaw Reverses. Simply Back the Jaw Out, Turn it Around and Re-Insert. Serrations on the Inside Edge Form a Deep Tooth Pattern that Hold Pipe Tight and Reduce Slipping
- Corrosion Resistant Black-Phosphate Finish
- Packaged in a Convenient Storage Tray

Literature http://www.apex-tools.eu/sites/default/files/multisite_brochures_pdf/Crescent%20Group_Catalogue%202018.pdf

