## **Cutting tweezers**

<ul> <li>Suitable for cutting fine, soft wires and small components</li> <li>Delivers high-precision cuts</li> <li>Hardened cutting edges for long service life</li> </ul>		<ul> <li>For all models with the suffix S in the order number: Stainless steel, robust tips, non-rusting, non-reflecting surface</li> </ul>			
4.528 Inch / 115 mm	Model	Weight		Material	Description
		OZ.	g		
The set	15AGW	0.92	26	Stainless steel	Cutting tweezers with narrow oblique head. For soft wires up to dia. 0.25 mm/.010 Inch.
and the	15AGS	0.74	21	Stainless steel	Cutting tweezers with narrow oblique head. For soft wires up to dia. 0.25 mm/.010 Inch.