


Product datasheet

Technical data

Electrical data

Nominal voltage	230 V
Mains frequency	50/60 Hz
System wattage	4.00 W

Dimensions & weight



Height	21.0 mm
Product weight	69.00 g
Mounting hole spacing, length	180.0 mm

Temperatures & operating conditions

Ambient temperature range	0...+50 °C
---------------------------	------------

Capabilities

Dimmable	No
Dimming interface	DALI
Number of control outputs	1
Type of installation	Luminaire integration

Certificates & standards

Type of protection	IP20
Protection class	II

Logistical data





Commodity code	853710989900
----------------	--------------

Product datasheet

Equipment / Accessories

- Independent installation in connection with LMS CI BOX
-

Download Data

File	
	Declarations of conformity DALI REP LI SO CE 3560605 020321
	Operating instructions 336809_DALI REPEATER LI OPERATING INSTRUCTION (GB)
	CAD data 3-dim 321295_DIM MULTI 3 - DALI REP LI - DALI MULTI 3 - DALI EASY III - TOUCH DIM RC
	CAD data PDF 321293_DALI MULTI 3 - DALI EASY III - DIM MULTI 3 - DALI REP LI

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4008321292599		Shipping carton box 25	232 mm x 225 mm x 196 mm	10.23 dm ³	2755.60 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.
