

DIGITUS HDMI Ultra High Speed Connection Cable

DB-330124-010-S
EAN 4016032472018



HDMI Ultra High Speed connection cable, type A M/M, 1.0m, w/Ethernet, UHD 8K 60Hz, gold, bl

With this cable standard, the ultra high speed HDMI cable supports all current requirements – from the transmission of high-resolution UHD 8K content, two-way audio transmission (ARC) and control of HDMI devices via CEC. Internet applications can also be used without the additional need to connect an Ethernet cable (HEC). Lip Sync means that delayed lip movement is a thing of the past. This cable can also be used to transmit up to 32 audio channels and enjoy image output in 21:9 CinemaScope format. Get more out of your Blu-ray player, gaming console or HD streaming portal. Gold-plated contacts and triple shielding of the cable ensure maximum conductivity and interference-free transmission. Also supports 4K 3D in 50/60 Hz.

This cable already meets the requirements of future high-definition devices (TV, beamer, monitor) of the next generation, with higher resolutions, higher data rates and higher frame refresh rates.

- Support up to 8K with 60Hz
- Support of 4K 3D with 50/60Hz
- Support of 14 and 16 bit color dept
- Support of HDR (High Dynamic Range)
- Support Audio Return Channel (ARC)
- Support Consumer Electronic Control (CEC)
- Support Lip-Sync (audio/video synchronisation)

- Dolby TrueHD capable
- Multi Stream audio/video support
- 21:9 Cinemascope support
- 32 Channel Audio support
- With Ethernet Channel (HEC)
- Supports 120 Hz @ 1920 x 1080p resolution
- Supports 4K 50/60 Hz
- Supports 1080p 3D HFR
- Supports Deep Color 30bit
- Supports DTS-HD-Master-Audio-Bitstream
- Supports Super-Audio-CD (DSD)
- Supports DVD-Audio
- Supports Blu-Ray Disc and HD-DVD Audio- and Video
- Color cable: black
- Connector 1: HDMI type A, plug
- Connector 2: HDMI type A, plug
- Connector surface: gold-plated
- Ferrite filter: none
- HDMI Standard: Ultra High Speed HDMI
- HDTV Resolution max.: 7680 × 4320 Pixel, 60Hz
- HDTV Standard: Ultra HD 8K
- Hoods: plastic
- Length: 1 m
- Length: 1 m
- AOC - Active Optical Cable: no

Logistics						
	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm ³
Packaging Unit Carton	100	16.75	55.00	54.80	20.50	61,787.00
Packaging Unit Inside	10	1.68	28.00	36.00	25.00	25,200.00
Packaging Unit Single	1	0.17	16.00	3.00	14.00	672.00
Net single without Packaging	1	0.09	14.00	3.00	13.00	546.00

More images:

