



Designed for full mobile management

DCP-J1200W



PRINT



COPY



SCAN



WIRELESS

www.brother.eu

Mobile managed All-in-one wireless colour inkjet printer

Revolutionise your print and scan experience with the DCP-J1200W, which is designed for the modern day user.

A multifunction printer offering print, copy and scan functionality with wireless connectivity, you can fully operate this printer from your mobile device. By downloading Brother Mobile Connect to iOS or Android you can manage your printing device from anywhere.

DCP-J1200W



Key Features:

- Mobile managed - download app: 'Brother Mobile Connect'
- Wireless connectivity
- Enclosed paper tray holding up to 150 sheets
- Print speeds of up to 16ipm mono and 9ipm in colour
- Copy and scan in colour
- Inbox inks – BK: 720 pages, CMY 480 pages



Print from anywhere, any time

Thanks to the remote print function on the Brother Mobile Connect app, you can send prints jobs from anywhere – allowing you to get on with the rest of your day. You can even set up notifications that'll let you know when the job is completed.

Brother Mobile Connect

Mobile Connect is the app that let's you personalise your frequently used printer functions unlocking a revolutionary way of printing. As well as sending print job from anywhere, there is whole host of useful scan features – scanned data directly to your mobile device or check your scan history for files. If you're worried about running out of supplies simply check ink levels, order replenishment supplies direct to your door.

General

CPU speed

576MHz

Display

LED

Memory Capacity

128MB

Ink Page Gauge

Yes

Paper

Standard Tray

150 sheets (80 g/m²)

Output Paper Capacity

50 sheets (80 g/m²)

Media Sizes/Standard Tray

50 (80 g/m²)A4, LTR, EXE, A5, A6, Photo (102x152mm/4x6"), Indexcard (127x203mm/5x8"), Photo-2L (127x178mm/5x7"), C5 Envelope, Com-10, DL Envelope, Monarch

Media Types & Weights/ Standard Tray

Plain, Inkjet, Glossy(cast/resin), Recycled & 64-220g/m² (17-58 lb.)

Media Sizes/Scanner Glass (width/length)

up to 215.9/297mm
(up to 8.5/11.7")

Media Sizes/Manual Duplex

<PC Print>
A4/LTR/EXE/A5
<Copy>
Letter/A4/A5/EXE

Media Types & Weights/ Manual Duplex

Plain & 64-105g/m²
(17-28lb)

Print

Print Speed¹

16.0 mono / 9.0ipm colour

First Print Out Time²

10.0 sec mono / 6.5 sec colour

Resolution (horizontal x vertical)

Up to 1200x6000 dpi
Windows[®] only
(Mac: Up to 1200x3600 dpi)

Emulation

GDI

Quiet Mode

Yes

Print Function

N-up Printing³

Reduce up to 2, 4, 9 or 16 A4 pages into just one A4 page
Reduce up to 2, 4, 9 or 16 A4 pages into just one A4 page

Poster Printing⁴

Enlarge 1 A4 page into a poster using 4, 9, 16 or 25 A4 pages

Watermark Printing⁴

Watermark your documents with predefined text or with your own user-defined messages

ID Printing⁴

Add identification to your printed documents (date & time, short custom message or PC username)

Manual 2-Sided Print⁴

Manual 2-sided printing (recommended for media not supported by automatic 2-sided print)

Booklet Printing⁴

Print documents in A5 booklet format using manual 2-sided print

Print Profiles³

Store your favourite driver settings as profiles to easily recall them

Copy

Copy Speed⁵
8.0ipm mono / 3.0ipm colour

First Copy Out Time⁶
11.5 sec mono /
27.0 sec colour

**Resolution
(horizontal x vertical)/Mono**
Print: Max. 1200 x 1800dpi
Scan: Max. 1200 x 1200dpi

**Resolution
(horizontal x vertical)/Color**
Print: Max. 1200 x 1800dpi
Scan: Max. 1200 x 600dpi

Remote Copy
Yes

Reduction/Enlargement (%)
25 - 400 in 1% increments
(Remote Copy)

N in 1
2in2in1/2in1(ID)/4in1
(Remote Copy)(ID)

Poster
Yes (3x3)
(Remote Copy)

Scan

Scanner Type
CIS (Contact Image Sensor)

Colour & Mono Scanning
Yes

**Scan speed (Mono/Color)
*@100dpi**
A4: 3.35s/4.38s

**Resolution(horizontal x
vertical)/Optical**
FB: 1200x2400 dpi

**Multi-page Scan to Single
PDF files (Firm/PC)**
Yes (iPrint&Scan Desktop Only)

Auto Crop (Firm/PC)
Yes (TWAIN only)

**Base Color Removal
(Firm/PC)**
Yes

**Document Scanning width/
length**
FB: 213.9mm (8.42in)/ 295mm
(11.61in)

Color Depth (Input/Output)
Color Depth
30bit color Processing (Input)
24 bit color Processing (Output)
/256 levels per color
Gray Scale
10bit color Processing (Input)
8bit color Processing (Output)
/256 levels

Scan Functions

Scan to Image
Scan into your preferred
image editing software

Scan to OCR
Scan documents directly into
your word processing
application for instant editing

Scan to Email
Scan and share documents
via e-mail

Scan to File
Scan to a file on your computer

Scan Drivers

Windows[®]
TWAIN & WIA
Windows[®]
Windows[®] 10
Windows[®] 8
Windows[®] 11

Macintosh⁷
TWAIN
macOS 10.8.x or greater

Connectivity

USB Interface

Hi-Speed USB 2.0

Wireless Network

IEEE 802.11b/g/n
(Infrastructure)

Wireless Direct

IEEE 802.11g/n
(Wireless Direct)

Brother Mobile Connect⁷

print
scan
copy preview
machine settings

AirPrint

Yes

Mopria⁷

Yes

Brother Print Service Plugin⁷

Yes

Network & Security

Wireless Network Security

SSID (32 chr), WEP 64/128bit, WPA-PSK(TKIP/AES), WPA2-PSK(TKIP/AES), SSL/TLS (IPPS, HTTPS)

IP Filter

IPv4

Protocols (IPv4)

ARP, RARP, BOOTP, DHCP, APIPA(Auto IP), WINS/NetBIOS name resolution, DNS Resolver, mDNS, LLMNR responder, LPR/LPD, Custom Raw Port/Port9100, IPP, SNMPv1/v2c, TFTP server, ICMP, Web Services (Print/Scan), SNTP Client, HTTP Server.

Protocols (IPv6)

NDP, RA, mDNS, LLMNR Responder, DNS Resolver, LPR/LP, Custom Raw Port/Port9100, IPP, SNMPv1/v2c, TFTP server, Web Services (Print/Scan), SNTP Client, ICMPv6, HTTP Server

Network Management

BRAdmin Windows Only
(by download)

Embedded Web Server (EWS)

Yes
(Recommend Browser: Internet Explorer 11/Edge (for Windows), Safari 10/11 (for Mac), Chrome (for Android), Chrome/Safari (for iOS)
Recommend OS: 4.x or later (for Android), 10.x or later (for iOS))

Supplies and Accessories

Inbox Cartridges⁸

LC424BK – 720 pages
LC424CMY – 480 pages

Replacement cartridges⁸

LC424BK – 750 pages
LC424CMY – 750 pages

Duty Cycle

Recommended monthly volume⁹

50 to 1,000 pages

Maximum Monthly Volume⁹

Up to 2,500 pages

Dimensions

Carton Dimension

W 506 x D 219 x H 469mm

Carton Weight

7.7kg

Machine Dimensions

W 435 x D 359 x H 161mm

Machine Weight

6.5kg

Environment

Power Consumption

Networked Standby: Approx. 1.1W
Copying Mode: Approx. 13W
Ready Mode: Approx. 2.5W
Sleep Mode: Approx. 0.8W
Off: Approx 0.2W

Sound Pressure Level (Operating)

56dB(A) (Approx.)
*Noise depends on printing conditions.

Sound Power Level (Printing)

6.71B(A)

GS mark (Germany)

Yes

1. Based on ISO/IEC 24734
2. Based ISO/IEC 17629
3. Windows & Mac Only
4. Windows Only
5. Based on ISO/IEC 29183
6. Based on ISO/IEC 24735
7. Optional Download
8. Approx declared yield value in accordance with ISO/IEC 24711
9. Maximum number of printed pages per month can be used to compare designed durability between like Brother products. For maximum printer life, it is best to choose a printer with a duty cycle that far exceeds your print requirements



Working with you for a better environment

At Brother, our green initiative is simple. We strive to take responsibility, act respectfully and try to make a positive difference to help build a society where sustainable development can be achieved. We call this approach Brother Earth.

www.brotherearth.com

All specifications correct at the time of printing and are subject to change. Brother is a registered trademark of Brother Industries Ltd. Brand product names are registered trademarks or trademarks of their respective companies.

brother
at your side