Monthly Duty Cycle (max)
Recommended Monthly Volume

Manuf. part number DCPL8410CDWG1

Manufacturer Brother





## **Brother DCP-L8410CDW - Multifunction printer**

Product information	
Manufacturer	Brother
Manuf. part number	DCPL8410CDWG1
Main specifications	
Product Description	Brother DCP-L8410CDW - multifunction printer (colour)
Device Type	Printer / copier / scanner
Bundled Services	Brother PRINT AirBag for 200000 pages
Localisation	German
Printing Technology	Laser (colour)
Monthly Duty Cycle (max)	40000 pages
Recommended Monthly Volume	3000 pages
Max Copying Resolution	Up to 1200 x 600 dpi (mono) / up to 1200 x 600 dpi (colour)
Max Printing Speed	Up to 31 ppm (mono) / up to 31 ppm (colour)
Max Printing Resolution	Up to 2400 x 600 dpi (mono) / up to 2400 x 600 dpi (colour)
Scanning	1200 x 2400 dpi
Original Type	Sheets
Document Feeder Capacity	50 sheets
Media Size	76.2 x 127 mm (min) - Legal (216 x 356 mm), A4 (210 x 297 mm) (max)
Media Type	Plain paper, labels, recycled paper, thin paper, thick paper, glossy paper
Standard Media Capacity	300 sheets
Max Media Capacity	1050 sheets
Bypass Feeder Capacity	50 sheets
Output Trays Capacity	150 sheets
Automatic Duplexing	Yes (copying) Yes (printing) Yes (scanning)
PC Connection Availability	Yes
PC Connection	USB 2.0, Gigabit LAN, Wi-Fi(n), USB host
AirPrint Enabled	Yes
Office Machine Features	Print from USB flash drive, scan to e-mail, scan to FTP, scan to SMB, scan to SharePoint, Google Cloud Print 2.0, scan to USB host, scan to e-mail server
Dimensions (WxDxH)	43.5 cm x 52.6 cm x 53.9 cm
Weight	27.6 kg
Environmental Standards	ENERGY STAR Qualified, Blue Angel
General	
Device Type	Printer / copier / scanner
Bundled Services	Brother PRINT AirBag for 200000 pages
Printing Technology	Laser - colour

40000 pages

3000 pages

Manuf. part number DCPL8410CDWG1

Manufacturer Brother

### Continued

# **Brother DCP-L8410CDW - Multifunction printer**







Colour Support	Colour	`
Display Features	Touch screen	
PC Connection Availability	Yes	
PC Connection	USB 2.0, Gigabit LAN, Wi-Fi(n), USB host	
AirPrint Enabled	Yes	
Office Machine Features	Print from USB flash drive, scan to e-mail, scan to FTP, scan to SMB, scan to SharePoint, Google Cloud Print 2.0, scan to USB host, scan to e-mail server	
Localisation	German	
Memory		
Standard Memory	512 MB	
Copying		
Max Copying Resolution	Up to 1200 x 600 dpi (mono) / up to 1200 x 600 dpi (colour)	
Max Document Enlargement	400%	
Max Document Reduction	25%	
Maximum Copies	99	
Automatic Duplexing	Yes	
Printing		
Max Printing Resolution	Up to 2400 x 600 dpi (mono) / up to 2400 x 600 dpi (colour)	
Max Printing Speed	Up to 31 ppm (mono) / up to 31 ppm (colour)	
Printer Drivers / Emulations	PCL 6, PostScript 3, PDF 1.7, XPS	
Automatic Duplexing	Yes	
First Print Out Time B/W	15 sec	
First Print Out Time Colour	15 sec	
Scanning		
Scan Element	CIS	
Automatic Duplexing	Yes	
Optical Resolution	1200 x 2400 dpi	
Interpolated Resolution	19200 x 19200 dpi	
Grey Scale Depth	8 bit	
Colour Depth	24 bit	
Document & Media Handling		
Original Type	Sheets	
Document Feeder Capacity	50 sheets	
Min Media Size	76.2 x 127 mm	
Max Media Size	A4/Legal	
Min Media Weight	60 g/m <sup>2</sup>	
Max Media Weight	163 g/m²	
Supported Media Type	Plain paper, labels, recycled paper, thin paper, thick paper, glossy paper	
		/

Manuf. part number DCPL8410CDWG1

Manufacturer Brother

### Continued

Environmental Standards
ENERGY STAR Certified

Blue Angel Compliant

Dimensions & Weight

## **Brother DCP-L8410CDW - Multifunction printer**





Supported Media Sizes	ANSI A (Letter) (216 x 279 mm), Legal (216 x 356 mm), Executive (184 x 267 mm), A4 (210 x 297 mm), A5 (148 x 210 mm), A6 (105 x 148 mm), Folio (216 x 330 mm)
Standard Media Capacity	300 sheets
Max Media Capacity	1050 sheets
Bypass Feeder Capacity	50 sheets
Output Trays Capacity	150 sheets
Document & Media Handling Details	ADF - 50 sheets Input tray - 250 sheets - Legal (216 x 356 mm) weight: 60 g/m² - 105 g/m² Bypass tray - 50 sheets size: 76.2 x 127 mm - Legal (216 x 356 mm) weight: 60 g/m² - 163 g/m² Output tray - 150 sheets
Speed Details	Printing: up to 31 ppm - B/W Printing: up to 31 ppm - colour Printing: up to 14 spm - B/W duplex Printing: up to 14 spm - colour duplex Scanning: up to 28 ppm - B/W Scanning: up to 28 ppm - colour
Connections	
Interfaces	1 x USB 2.0 - 4 pin USB Type B 1 x USB host - 4 pin USB Type A 1 x Gigabit LAN - RJ-45
Security Protocols & Features	Kerberos, LDAP, SSL, WEP, WPA-PSK, TLS, IPsec, 802.1x, WPA2-PSK, TKIP, AES, ARP, TTLS
Power	
Power Consumption Operational	580 Watt
Power Consumption Standby	70 Watt
Power Consumption Sleep	10 Watt
Miscellaneous	
Warm Up Time	31 sec
First Copy Out Time B/W	17 sec
First Copy Out Time Colour	17 sec
Consumables Included	1 x Cartridge (black) - up to 3000 pages ISO/IEC 19798 1 x Cartridge (cyan) - up to 1800 pages ISO/IEC 19798 1 x Cartridge (magenta) - up to 1800 pages ISO/IEC 19798 1 x Cartridge (yellow) - up to 1800 pages ISO/IEC 19798 1 x drum - up to 50000 pages - Brother DR421CL 1 x transfer upit - up to 130000 pages - Brother BLI330CL

Yes

Yes



1 x transfer unit - up to 130000 pages - Brother BU330CL 1 x waste toner collector - up to 50000 pages - Brother WT320CL

Manuf. part number DCPL8410CDWG1

Manufacturer Brother

## Continued

# **Brother DCP-L8410CDW - Multifunction printer**





Width	43.5 cm
Depth	52.6 cm
Height	53.9 cm
Weight	27.6 kg
Dimensions & Weight (Shipping)	
Shipping Width	66.3 cm
Shipping Depth	54.2 cm
Shipping Height	65.4 cm
Shipping Weight	33.3 kg
Environmental Parameters	
Sound Emission	49 dBA (operating)