

## Brother DCP-1610W multifunctional Laser A4 2400 x 600 DPI 20 ppm Wi-Fi

**Brand :** Brother

**Product code:** DCP-1610W

**Product name :** DCP-1610W

DCP-1610W - Print/Copy/Scan, A4, 2400x600 dpi, USB 2.0, 802.11b/g/n, GDI, 32MB, 7.2kg

[Brother DCP-1610W multifunctional Laser A4 2400 x 600 DPI 20 ppm Wi-Fi:](#)

### Effortless printing with no complications

The Brother DCP-1610W is stylishly designed and compact enough to fit onto a shelf or workstation. It produces outputs with the speed and quality you would expect from a more expensive machine. Installation is very easy – connect using wireless or the USB cable, and you will be printing in no time. Plus innovative Anti-Jam technology allows you to print wirelessly with no hassle. You will also be able to print at speeds of up to 20 pages per minute (ppm), and your first page will come out in less than 10 seconds.

- Print, copy and scan
- Up to 20ppm print speed
- Wireless ready
- 2,400 x 600dpi resolution
- 150-sheet paper tray
- Innovative anti-jam technology.



Printing		Network		
Print technology *	Laser	Supported network protocols (IPv6)	NDP, RA, DNS Resolver, mDNS, LLNMR responder, LPR/LPD, Custom Raw Port/ Port 9100, IPP, FTP Server, SNMPv1/v2c, HTTP Server, TFTP Client/Server, SMTP Client, ICMPv6, Web Services	
Printing *	Mono printing		Mobile printing technologies	Brother iPrint & Scan
Duplex printing *	✗		<b>Performance</b>	
Maximum resolution *	2400 x 600 DPI		Card reader integrated	✗
Print speed (black, normal quality, A4/US Letter) *	20 ppm		Internal memory *	32 MB
Time to first page (black, normal)	10 s		Built-in processor	✓
<b>Copying</b>		Processor frequency	200 MHz	
Duplex copying *	✗	Sound pressure level (printing)	52 dB	
Copying *	Mono copying	<b>Design</b>		
Maximum copy resolution *	600 x 600 DPI	Product colour *	Black, White	
Copy speed (black, normal quality, A4)	20 cpm	Market positioning *	Home & office	
Maximum number of copies	99 copies	Built-in display *	✓	
Copier resize	25 - 400%	Display	LCD	
N-in-1 copy function (N=)	2,4	Display number of lines	2 lines	
<b>Scanning</b>		Display number of characters	16	
Duplex scanning *	✗	<b>Power</b>		
Scanning *	Colour scanning	Power consumption (max)	1080 W	
Optical scanning resolution *	600 x 1200 DPI	Power consumption (average operating)	390 W	
Maximum scan resolution	19200 x 19200 DPI	Power consumption (PowerSave)	0,9 W	
Maximum scan area	A4 (210 x 297)	Power consumption (ready)	50 W	
Scan technology	CIS	Power consumption (off)	0,28 W	
Scan to	E-mail, File, Image	AC input voltage	220 - 240 V	
Scan drivers	ICA, TWAIN, WIA	AC input frequency	50 - 60 Hz	
<b>Fax</b>				
Duplex faxing	✗			
Faxing *	✗			

Features		System requirements	
Recommended duty cycle	250 - 1800 pages per month		Windows 7 Home Basic, Windows 7 Home Basic x64, Windows 7 Home Premium, Windows 7 Home Premium x64, Windows 7 Professional, Windows 7 Professional x64, Windows 7 Starter, Windows 7 Starter x64, Windows 7 Ultimate, Windows 7 Ultimate x64, Windows 8, Windows 8 Enterprise, Windows 8 Enterprise x64, Windows 8 Pro, Windows 8 Pro x64, Windows 8.1, Windows 8.1 Enterprise, Windows 8.1 Enterprise x64, Windows 8.1 Pro, Windows 8.1 Pro x64, Windows 8.1 x64, Windows Vista Business, Windows Vista Business x64, Windows Vista Enterprise, Windows Vista Enterprise x64, Windows Vista Home Basic, Windows Vista Home Basic x64, Windows Vista Home Premium, Windows Vista Home Premium x64, Windows Vista Ultimate, Windows Vista Ultimate x64, Windows XP Home, Windows XP Home x64, Windows XP Professional, Windows XP Professional x64
Number of print cartridges *	1		Mac OS X 10.7 Lion, Mac OS X 10.8 Mountain Lion, Mac OS X 10.9 Mavericks
Printing colours *	Black		Linux operating systems supported ✓
Page description languages	GDI		Server operating systems supported
<b>Input &amp; output capacity</b>			
Total input capacity *	150 sheets		
Total output capacity *	50 sheets		
<b>Paper handling</b>			
Maximum ISO A-series paper size *	A4		
Paper tray media types *	Plain paper, Recycled paper	Windows operating systems supported	
ISO A-series sizes (A0...A9) *	A4, A5, A6		
ISO B-series sizes (B0...B9)	B5		
Non-ISO print media sizes	Executive, Folio, Legal, Letter		
Custom media length	148 - 355,6 mm		
Paper tray media weight	65 - 105 g/m <sup>2</sup>		
<b>Ports &amp; interfaces</b>			
Standard interfaces	USB 1.1, USB 2.0, Wireless LAN		
USB port	✓		
USB 1.1 ports quantity	1		
USB 2.0 ports quantity	1		
<b>Network</b>			
Wi-Fi *	✓		
Ethernet LAN *	✗	Mac operating systems supported	
Wi-Fi standards	802.11b, 802.11g, Wi-Fi 4 (802.11n)		
Security algorithms	128-bit WEP, 64-bit WEP, SMTP-AUTH, WPA-AES, WPA-PSK, WPA-TKIP, WPA2-AES, WPA2-PSK, WPS	Linux operating systems supported	✓
Supported network protocols (IPv4)	ARP, RARP, BOOTP, DHCP, APIPA (Auto IP), WINS/NetBIOS, DNS resolver, mDNS, LLNMR responder, LPR/LPD, Custom Raw Port/Port 9100, IPP, FTP Server, SNMPv1/v2c, HTTP Server, TFTP Client/Server, SMTP Client, ICMP, Web Services	Server operating systems supported	Windows Server 2003, Windows Server 2003 x64, Windows Server 2008, Windows Server 2008 R2, Windows Server 2008 x64, Windows Server 2012, Windows Server 2012 R2 x64
<b>Operational conditions</b>			
Operating relative humidity (H-H)	20 - 80%		
Storage temperature (T-T)	0 - 40 °C		
Operating temperature (T-T)	10 - 32 °C		
Storage relative humidity (H-H)	35 - 85%		
<b>Sustainability</b>			
Sustainability certificates	ENERGY STAR		
<b>Weight &amp; dimensions</b>			
Width	385 mm		
Depth	340 mm		
Height	255 mm		
Weight	7,2 kg		
<b>Packaging data</b>			
Package width	481 mm		
Package depth	436 mm		
Package height	406 mm		
Package weight	9 kg		
<b>Packaging content</b>			
Bundled software	Brother BRAdmin Light Network Management		
<b>Other features</b>			
Energy saving mode	✓		



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.