



DELL 22 Monitor - P2222H

Brand : DELL

Product code: DELL-P2222H

Product name : 22 Monitor - P2222H

- 54.6cm (21.5") Full HD 1920 x 1080 LED IPS
- 8ms, 16:9, 250cd/m², 1000:1
- USB, VGA, HDMI, DisplayPort
- 54.6cm (21.5") Full HD 1920 x 1080 LED IPS, 16:9, 250cd/m², 16.7M, 8ms, 178°/178°, 1000:1

DELL 22 Monitor - P2222H:

Stay productive no matter where you work. Reduce harmful blue light with this sleek 21.5-inch FHD monitor featuring ComfortView Plus technology.

DELL 22 Monitor - P2222H. Display diagonal: 54.6 cm (21.5"), Display resolution: 1920 x 1080 pixels, HD type: Full HD, Display technology: LCD, Response time: 8 ms, Native aspect ratio: 16:9, Viewing angle, horizontal: 178°, Viewing angle, vertical: 178°. Built-in USB hub, USB hub version: 3.2 Gen 1 (3.1 Gen 1). VESA mounting, Height adjustment. Product colour: Black, Silver



Display		Ports & interfaces	
Display diagonal *	54.6 cm (21.5")	HDCP	✓
Display brightness (typical)	250 cd/m ²	AC (power) in	✓
Display resolution *	1920 x 1080 pixels	Ergonomics	
Native aspect ratio *	16:9	Panel mounting interface	100 x 100 mm
Response time	8 ms	Cable lock slot *	✓
HD type *	Full HD	VESA mounting *	✓
Display technology *	LCD	Height adjustment *	✓
Backlight type	LED	Height adjustment	15 cm
Anti-glare screen	✓	Pivot	✓
Screen shape *	Flat	Pivot angle	-90 - 90°
Supported graphics resolutions	1920 x 1080 (HD 1080)	Swivelling	✓
Supported video modes	480p,576p,720p,1080i,1080p	Swivel angle range	-45 - 45°
Aspect ratio	16:9	Tiltable	✓
Contrast ratio (typical) *	1000:1	Tilt angle range	-5 - 21°
Maximum refresh rate *	60 Hz	On Screen Display (OSD)	✓
Viewing angle, horizontal	178°	Plug and Play	✓
Viewing angle, vertical	178°	LED indicators	Power
Display number of colours *	16.7 million colours	Power	
Panel type *	IPS	Energy efficiency class (SDR) *	D
Response time (fast)	5 ms	Energy consumption (SDR) per 1000 hours *	12 kWh
Pixel pitch	0.248 x 0.248 mm	Power consumption (standby) *	0.3 W
Pixel density	102 ppi	Power consumption (max)	46 W
Horizontal scan range	30 - 83 kHz	Power consumption (off)	0.2 W
Vertical scan range	56 - 76 Hz	AC input voltage	100 - 240 V
Viewable size, horizontal	47.6 cm	AC input frequency	50/60 Hz
Viewable size, vertical	26.8 cm	Energy efficiency scale	A to G
Viewable size diagonal	54.6 cm		
Display diagonal (metric)	54.61 cm		
sRGB coverage (typical)	99%		

Performance		Operational conditions	
Flicker-free technology	✓	Operating temperature (T-T)	0 - 40 °C
Low Blue Light technology	✓	Storage temperature (T-T)	-20 - 60 °C
Multimedia		Operating relative humidity (H-H)	10 - 80%
Built-in speaker(s) *	✗	Storage relative humidity (H-H)	5 - 90%
Built-in camera *	✗	Operating altitude	0 - 5000 m
Design		Non-operating altitude	0 - 12192 m
Market positioning *	Home	Sustainability	
Product colour *	Black, Silver	Sustainability certificates	ENERGY STAR, EPEAT Gold, RoHS
Front bezel colour	Black	Doesn't contain	PVC/BFR
Detachable stand	✓	Weight & dimensions	
Feet colour	Silver	Width (with stand)	487.3 mm
Heavy metals free	Hg (mercury)	Depth (with stand)	179.6 mm
Ports & interfaces		Height (with stand)	482 mm
Built-in USB hub *	✓	Weight (with stand)	4.57 kg
USB hub version	3.2 Gen 1 (3.1 Gen 1)	Width (without stand)	48.7 cm
USB upstream port type	USB Type-B	Depth (without stand)	5.21 cm
Number of upstream ports	1	Height (without stand)	29 cm
USB Type-A downstream ports quantity	4	Weight (without stand)	2.82 kg
VGA (D-Sub) ports quantity	1	Bezel width (side)	5.6 mm
HDMI *	✓	Bezel width (top)	5.6 mm
HDMI ports quantity	1	Bezel width (bottom)	1.66 cm
HDMI version	1.4	Packaging data	
DisplayPorts quantity	1	Stand included	✓
DisplayPort version	1.2	Cables included	AC, DisplayPort, HDMI, USB, VGA
Headphone out *	✗	Quick start guide	✓
		Package weight	6.37 kg



Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.