

## KPG 10



250°C HEAT RESISTANT KEVLAR® GLOVE - 10 CM WRIST

Ref. KPG10



### Product specifications

Kevlar® Technology outside. 100% cotton lining. Gauge 7.

Outside 100% Kevlar® (short fibers). Inside 100 % Cotton. Kevlar® is a DuPont registered trademark.

#### COLOUR

Yellow

#### SIZE

09

### Product Use - Risks



Heat



Cutting / Perforation



Wearing



Light industry

## Product's highlights & user's benefits



Knitted Kevlar® gauge 7:

- Optimal cut performance and good resistance to heat
- Excellent balance between heat resistance and dexterity



Ambidextrous  
Washable

10-cm knitted wrist :  
• Better vein protection



Cut level D



Cut level 5

## Certifications and Standards



DIRECTIVA EPI 89/686/CEE

EN420:2003+A1:2009 General requirements  
2: Dexterity (from 1 to 5)

EN388:2003 Protective gloves against mechanical Risks (Levels obtained on the palm)

1: Resistance to abrasion (from 1 to 4)  
5: Resistance to cutting (from 1 to 5)  
4: Resistance to tear (from 1 to 4)  
x: Resistance to puncture (1 to 4)



EN407:2004 Protective gloves against Heat & Fire risks (X = Unrealized test)

4: Resistance to flammability (from 1 to 4)  
2: Resistance to contact heat (from 1 to 4)  
X: Resistance to convective heat (from 1 to 4)  
X: Resistance to radiant heat (from 1 to 4)  
X: Resistance to small projections of liquid metal (from 1 to 4)  
X: Resistance to large projections of molten metal (from 1 to 4)



## References

References	Bar code	COLOUR	SIZE		
KPG1009	3295249035433	Yellow	09	36	6