

TW400 S3 SRC



FULL GRAIN LEATHER BOOTS - S3 HRO HI CI SRC

Ref. TW400S3



Product specifications

Upper: Full grain leather, S3 water resistant treatment, mit rubber scuff cap. Lining: Polyamide absorbing.
Insole: Removable preformed - Polyester on PU. Midsole: Cemented - PU with Panoshock® shock absorber.
Outsole: Rubber Nitrile. Non metallic footwear.

COLOUR

Black

SIZE

39, 40, 41, 42, 43, 44, 45, 46, 47, 48

Product Use - Risks



Antistatic



Heat



Shock



Cutting / Perforation



Slip



Agriculture / Green areas



Construction / Civil engineering



Mining

Product's highlights & user's benefits



PU/RUBBER OUTSOLE

- 1- Ladder grips
- 2- Flex-Zone for increased flexibility
- 3- Slip-resistant cleated outsole



Speed lace



Reinforced toe protection with Scuff Cap



Composite toe cap 200- joule,
Lighter than steel
Non conductive material



NON-METALLIC



Ultra flexible anti-perforation composite
insole



Preformed and removable insole: Polyester
on PU
Comfort and quick drying



PANOSHOCK® system
For reduced fatigue & added comfort

DELTA INNOVATION



COMPOSITE



Certifications and Standards



EN ISO 20344:2011 Personal protective equipment - Test methods for footwear

EN ISO 20345:2011 Personal protective equipment - Safety footwear.
S3 HRO HI CI: Additional special requirements
SRC: Slip resistance

References

References	Bar code	COLOUR	SIZE		
TW400S3NO39	3295249154400	Black	39	5	-
TW400S3NO40	3295249154417	Black	40	5	-
TW400S3NO41	3295249154424	Black	41	5	-
TW400S3NO42	3295249154431	Black	42	5	-
TW400S3NO43	3295249154448	Black	43	5	-
TW400S3NO44	3295249154455	Black	44	5	-
TW400S3NO45	3295249154462	Black	45	5	-
TW400S3NO46	3295249154479	Black	46	5	-
TW400S3NO47	3295249154486	Black	47	5	-
TW400S3NO48	3295249154493	Black	48	5	-