

PICAFLOR VE240



PICAFLOR 240 YELLOW LATEX CLEANING GLOVE

Ref. VE240



Product specifications

Latex with cotton flock lining.

Length: 30 cm.

Thickness: 0,38 mm.

Support: 100% natural latex.

Flocking: 100% cotton.

Tested according to EN374-3:2003 determination of permeation resistance, (Methanol : index 1/6, Sodium hydroxyde 40% (NaOH) : index 6/6, Sulphuric acid (96%) : index 2/6).

COLOUR

Yellow

SIZE

6/7, 7/8, 8/9, 9/10

Product Use - Risks



Biological chemical particles



Heavy industry



Light industry



Hygiene environment

CHEM D-FINDER



Certifications and Standards



EN420:2003 General requirements
5: Dexterity (from 1 to 5)

EN388:2003 Protective gloves against mechanical Risks (Levels obtained on the palm)

- 1: Resistance to abrasion (from 1 to 4)
- 0: Resistance to cutting (from 1 to 5)
- 1: Resistance to tear (from 1 to 4)
- 0: Resistance to puncture (1 to 4)





EN374-3 :2003 Protective gloves against chemicals and micro-organisms - Part 3:
Determination of resistance to permeation by chemicals



REGULATION (EU) 1935/2004 CONTACT WITH FOOD PRODUCTS

GLOB MIGR Food contact - Overall Migration
.: Contact with any type of food

References

References	Bar code	COLOUR	SIZE		
VE240JA06	3295249008680	Yellow	6/7	144	12
VE240JA07	3295249008697	Yellow	7/8	144	12
VE240JA08	3295249008703	Yellow	8/9	144	12
VE240JA09	3295249008710	Yellow	9/10	144	12