

## PHOCEA S3 SRC



PIGMENTED SPLIT LEATHER SHOES - S3 SRC

Ref. PHOCEAS3



### Product specifications

Upper: Pigmented split leather, S3 water resistant treatment. Lining: Polyamide mesh. Insole: Removable preformed - Polyamide on EVA. Outsole: Injected - PU bi-density. Non metallic footwear.

#### COLOUR

Black

#### SIZE

36, 37, 38, 39, 40, 41, 42, 43, 44, 45, 46, 47

## Product Use - Risks



Antistatic



Shock



Cutting / Perforation



Slip



Agriculture / Green areas  
craftman



Construction / Civil engineering



Second work /



Light industry



Services / Logistics



Mining

## Product's highlights & user's benefits



- 1- Flex-Zone
- 2- V STAB SYSTEM
- 3- Ladder lateral grips
- 4- Cleats with grip on all indoor and outdoor surfaces
- 5- Standards SRC



Ultra flexible anti-perforation composite insole



NON-MAGNETIC  
No metal part in the shoe



Composite toe cap 200- joule,  
Lighter than steel  
Non conductive material

Composite  
Protection

NON-METALLIC



Speed lace

COMPOSITE

COMPOSITE



## Certifications and Standards



EN ISO 20344:2011 Personal protective equipment - Test methods for footwear

EN ISO 20345:2011 Personal protective equipment - Safety footwear.  
S3: Additional special requirements  
SRC: Slip resistance

References

References	Bar code	COLOUR	SIZE		
PHOCES3NO36	3295249195762	Black	36	5	-
PHOCES3NO37	3295249195779	Black	37	5	-
PHOCES3NO38	3295249195793	Black	38	5	-
PHOCES3NO39	3295249195809	Black	39	5	-
PHOCES3NO40	3295249195816	Black	40	5	-
PHOCES3NO41	3295249195823	Black	41	5	-
PHOCES3NO42	3295249195830	Black	42	5	-
PHOCES3NO43	3295249195847	Black	43	5	-
PHOCES3NO44	3295249195854	Black	44	5	-
PHOCES3NO45	3295249195861	Black	45	5	-
PHOCES3NO46	3295249195878	Black	46	5	-
PHOCES3NO47	3295249195885	Black	47	5	-