



## V7 Dual Monitor Articulating Clamp Mount

### DM1GCD

SKU: CD96887

The DM1GCD from V7 supports dual displays up to 32" (81cm), and 20lbs (9kg). It enables you to have one display portrait and one in landscape mode. With 180° rotation, 45° tilt, and 90° swivel it provides flexible mounting solutions. It also can be mounted with a desk clamp or grommet for easy installation. It additionally features a detachable VESA plate for easy installation.

- Articulating dual mount set up for displays up to 32" (81cm), 9kg (20lbs)
- 180° rotation, 45° tilt, and 90° swivel provides flexible mounting solutions
- Desk clamp or grommet included as mounting options
- Detachable VESA plate design for easy installation
- Simultaneous portrait and landscape mode for productivity and efficiency

#### General

SKU: CD96887  
 Model: DM1GCD  
 EAN: 0662919114980  
 Warranty: 5 years  
 Compliance: RoHS  
 Country Of Origin: China  
 Package Type: One Color  
 ASIN: B09RK77VFP  
 SAP: 5443743  
 Package Includes: Mount, Hardware, Instruction manual

#### Design

Display Size (per display): 17" to 32" Displays  
 Mount Type: Desk Mount  
 Material: Steel  
 Weight Limit: 9 kg (19.8 lbs)

#### Package Dimensions

Package Dimensions (L/W/H): 41.5 x 19.5 x 11.5 cm  
 (16.3 x 7.7 x 4.5 in)  
 Shipping Weight: 4 kg (8.8 lbs)  
 Package Weight: 4 kg (8.8 lbs)

#### Product Dimensions

Product Dim (L/W/H): 86.9 x 11.2 x 56.1 cm (34.2 x 4.5 x 22.1 in)  
 Product Weight: 3.50 kg (7.7 lbs)

#### Technical

Tilt: +45° ~ -45°  
 Swivel: +90° ~ -90°  
 VESA Mount: 100 x 100 mm, 75 x 75 mm  
 Number of Displays: 2  
 Screen Rotation: +180° ~ -180°  
 Weight Limit (per display): 9 kg (19.8 lbs)