

DIGITUS Wall Mounting Cabinet, SOHO, unmounted - 540x400 mm (WxD)

DN-19 07U-S-1 EAN 4016032331698





7U wall mounting cabinet, SOHO, unmounted 370x540x400 mm, full glass front door, grey

The unmounted SOHO Wall Mounting Cabinets are made of a robust sheet steel construction with a minimum of seams. The enclosures are special designed to save a lot of space and costs while delivery due to the flat packaging. It is fast and easy to mount the cabinet. Due to their flexibility the cabinets are ideal for all current IT and telecommunication applications.

The DIGITUS® Professional Wall Mounting Cabinets are made for high demand IT-Infrastructure Solutions - designed and developed on highest standard in Germany

- Safety class rating IP20
- Lockable safety-glass door
- 200° door opening angle
- 1-point-locking-mechanism on the front door
- 483 mm (19") profile rails mounted on the front side inside of the cabinet, galvanized

- 483 mm (19") profile rails are adjustable in depth
- 1.1 1.5 strong sheet steel with a high loading capacity, powder coated
- Cable entry with brush strip on the top and with plastic cover on the base
- Roof is prepared for fan units (punched out entries)
- Ventilation slots for active and passive ventilation and exhausting
- Equipment mounting depth min.-max.: 170-270 mm
- IP protection class: IP20
- Color: light grey, RAL 7035
- Depth: 400 mm
- · Front door: Glass door, single opening
- Units: 7
- Load capacity: 60 kg
- Mounted: no
- Side panels: Both sides
- Cabinet type: Wall mounting cabinet
- Width: 540 mm

Logistics						
	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	1	11.60	42.50	63.00	7.00	18,742.50
Packaging Unit Inside	1	11.60	42.50	63.00	7.00	18,742.50
Packaging Unit Single	1	11.60	42.50	63.00	7.00	18,742.50
Net single without Packaging	1	10.82	42.50	63.00	7.00	18,742.50



More images:

