

# DIGITUS Wall Mounting Cabinets Dynamic Basic Series - 600x600 mm (WxD)

DN-19 09U-6/6-EC  
EAN 4016032221746



**9U wall mounting cabinet, Dynamic Basic 505x600x600 mm, color grey (RAL 7035)**

The Wall Mounting Cabinets of the Dynamic Basic Series are made of a robust steel construction. Stability is given due to the welding spots. The side sections are detachable and the installation on the wall is easy so it can be implemented quickly. Due to their flexibility the cabinets are ideal for all current IT and telecommunication applications.

- Safety class rating IP20
- Lockable safety-glass door with steel frame
- 210° door opening angle
- 1-point-locking-mechanism on the front door
- 483 mm (19") profile rails mounted on the front- and rear side inside of the rack, galvanized
- 483 mm (19") profile rails are adjustable in depth and with height unit marking

- 0.8 - 1.2 mm strong sheet steel with high load capacity, powder coated
- Cable entry on the rear side, roof and base (pre-punched break-outs)
- Roof is prepared for fan units (punched out entries)
- Ventilation slots for active and passive ventilation and exhausting
- 4 earthing points (base, side panel and front door) with protection cap
- IP protection class: IP20
- Color: light grey, RAL 7035
- Depth: 600 mm
- Front door: Glass door, single opening
- Units: 9
- Load capacity: 60 kg
- Mounted: yes
- Cabinet type: Wall mounting cabinet
- Width: 600 mm

| Logistics                    |              |             |            |            |             |                 |
|------------------------------|--------------|-------------|------------|------------|-------------|-----------------|
|                              | Number (pcs) | Weight (kg) | Depth (cm) | Width (cm) | Height (cm) | cm <sup>3</sup> |
| Packaging Unit Carton        | 1            | 26.50       | 63.00      | 63.00      | 53.00       | 210,357.00      |
| Packaging Unit Inside        | 1            | 26.50       | 63.00      | 63.00      | 53.00       | 210,357.00      |
| Packaging Unit Single        | 1            | 26.50       | 63.00      | 63.00      | 53.00       | 210,357.00      |
| Net single without Packaging | 1            | 24.45       | 63.00      | 63.00      | 53.00       | 210,357.00      |

**More images:**

