

DIGITUS Wall Mounting Cabinet Unique Series - 600x600 mm (WxD)

DN-19 16U-6/6
EAN 4016032174097



16U wall mounting cabinet, Unique 820x600x600 mm, color grey (RAL 7035)

The Wall Mounting Cabinets of the Unique Series were designed for the user friendly installation of active- and passive network components accompanied by a neat cable management. Each rack consists of up to 1.5 mm strong steel sheet material which ensures a very good stability as a robust steel construction. The color is created by powder coating in grey (RAL 7035) and black (RAL 9005). Wall installation can be done easily, there are two steps: Mount the rear wall of the housing on your wall and then simply connect it with the housing. Separately leveling feet or castors are available for free standing purposes. Door and side panels are easy to detach and the door stop can be changed from right to left. The roof contains air ventilation slots for a better air circulation. Each wall mounting cabinet contains one pair (two pieces) of mounted 483 mm (19") profile rails inside (wall mounting cabinets from 600 mm depth contain two pairs). They are galvanized, with height unit marking (countable from both directions) and variable in depth. An important aspect for each installation is the cable management. The roof of each cabinet is equipped with a sliding cable entry panel with rubber sealing. Punched out cable entries with plastic cover are present on the rear wall and base. An extensive portfolio of accessories for cable management, shelves, etc. will help to meet many requirements in daily use.

The DIGITUS® Professional Unique Series is made for high demand IT-Infrastructure Solutions - designed and developed on highest standard in Germany

- Safety class rating IP20
- Lockable safety-glass door with steel frame
- 210° door opening angle
- 1-point-locking-mechanism on the front door
- Side panels are lockable and removable
- 483 mm (19") profile rails mounted on the front- and rear side inside of the rack, galvanized
- 483 mm (19") profile rails are adjustable in depth and with height unit marking
- Max. installation depth: 450 mm
- Cable entry on the rear side and base with plastic cover and top with sliding cover
- Roof is prepared for fan units (punched out entries)
- Ventilation slots for active and passive ventilation and exhausting
- Several earthing points for rack components
- Incl. installation set (screws, cage nuts, washers)
- Rack is completely mounted
- Equipment mounting depth min.-max.: 320-450 mm
- IP protection class: IP20
- Color: light grey, RAL 7035
- Color: light grey, RAL 7035
- Depth: 600 mm
- Front door: Glass door, single opening
- Units: 16
- Load capacity: 100 kg
- Mounted: yes
- Cabinet type: Wall mounting cabinet
- Width: 600 mm

Logistics						
	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	1	38.00	65.00	65.00	87.00	367,575.00
Packaging Unit Inside	1	38.00	65.00	65.00	87.00	367,575.00
Packaging Unit Single	1	38.00	65.00	65.00	87.00	367,575.00
Net single without Packaging	1	35.77	65.00	65.00	87.00	367,575.00

More images:

