

# DIGITUS 24 Port Fast Ethernet Switch, Unmanaged

**DN-60021-2**  
**EAN 4016032451266**



### Fast Ethernet Switch 24-port, unmanaged

The DIGITUS® 24-Port Fast Ethernet switch makes 24 10/100 Mbps RJ-45 ports with auto negotiation available. All ports support the Auto MDI/MDIX function, which eliminate the need for crossover cables and uplink ports. Low costs, simple use and high performance are the strengths of the DIGITUS® Fast Ethernet 24-Port switch and thus make it an excellent choice for your network.

#### Ideal for sharing workgroups with multiple high-speed servers!

- 24 RJ45 ports
- Up to 20/200 Mbps in Full Duplex Mode
- Compatible to the following standards: IEEE 802.3, 802.3u, 802.3az and 802.3x
- Very low power consumption due to the EEE (Energy Efficient Ethernet) Technology
- Automatic cable detection - auto MDI / MDI-X function
- 8K MAC addresses
- Auto-negotiation of full- and half-duplex
- Power, link/active, speed indicators for network status

- Shielded metal housing
- Noiseless design - without fan
- Built-in Power Supply
- Suitable for rack mount (incl. mounting bracket)
- Ethernet speed: Fast Ethernet
- Industrial usage: no
- Number of ports: 24
- PoE (Power over Ethernet): no
- Protection against vandalism: no
- Managed: no
- Installation type: Desktop
- Outdoorsuitable: no
- VLAN: no

#### Package contents

- Switch
- Power Cable
- Manual
- Mounting accessories

| Logistics                    |              |             |            |            |             |           |
|------------------------------|--------------|-------------|------------|------------|-------------|-----------|
|                              | Number (pcs) | Weight (kg) | Depth (cm) | Width (cm) | Height (cm) | cm³       |
| Packaging Unit Carton        | 5            | 5.40        | 26.80      | 36.50      | 48.50       | 47,442.70 |
| Packaging Unit Inside        | 1            | 1.08        | 9.00       | 35.20      | 25.20       | 7,983.36  |
| Packaging Unit Single        | 1            | 1.08        | 9.00       | 35.20      | 25.20       | 7,983.36  |
| Net single without Packaging | 1            | 1.08        | 17.30      | 28.00      | 4.50        | 0.00      |

More images:

