

# DIGITUS QSFP+ 40G 10 m AOC cable

DN-81313  
EAN 4016032460121



**QSFP+ 40G 10m AOC cable**

**Allnet, CISCO, Dell, D-Link, Edimax, Etherwan, Fortinet,**

Active DIGITUS® 40G QSFP+ AOC cables are a high-performance, energy-saving, short-range connectivity solution that supports InfiniBand QDR/DDR/SDR, 12.5G/10G/8G/8G/4G/4G/2G fibre channels, PCIe and SAS. They are compliant with the QSFP MSA and IEEE P802.3ba. Four full-duplex channels are used, with each channel capable of transferring data at rates of up to 11.3 Gbps, thus ensuring an aggregated rate of 45.2 Gbps. Active DIGITUS® 40G QSFP+ AOC cables provide increased port density and cost savings in the overall system.

**High bandwidth without delays or signal loss**

- 10 m maximum distance
- 2.125-41.2 Gbps supported data rate
- Supported applications: 12.5G fibre channel, 10G fibre channel, 8G fibre channel, 4G fibre channel and 2G fibre channel

- Compatible brands: Allnet, CISCO, Dell, D-Link, Edimax, Etherwan, Fortinet, Intellinet, KTI Networks, Level One, Netgear, PLANET, Tenda, TP-Link, TRENDnet, ZyXEL, ZTE etc. compatible
- DDM/DOM support
- Temperature range: 0 to +70 °C
- Connectors: QSFP
- Power: +3.3 V supply voltage
- Power consumption: <1.5 W
- 850 nm wavelength multimode fibre
- Length: 10 m
- Connection: QSFP+
- DDM Support: no
- Ethernet speed: 40 Gigabit

**Package contents**

- QSFP+ 40G 10 m AOC cable
- Quick start guide

Logistics						
	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm <sup>3</sup>
Packaging Unit Carton	150	15.00	48.00	48.00	38.00	87,552.00
Packaging Unit Inside	1	0.10	26.00	26.00	2.00	1,352.00
Packaging Unit Single	1	0.10	26.00	26.00	2.00	1,352.00
Net single without Packaging	1	0.19	11.00	1.80	1.30	0.00