

DIGITUS Modular Patch Panel, 24-port

DN-91410
EAN 4016032280781



Modular Patch Panel, shielded 24-port, blank, 1U, rack mount, grey RAL 7035

The Modular Patch Panel from DIGITUS® is available as 16- or 24-port version. The 1.5 mm cold rolled c-steel provides the best storage of your Keystone Modules.

- Layout Keystone Entry: Straight
- Area of application: 483 mm (19") cabinet
- Norms: ISO/IEC 11801 3rd Ed., EN 50173-1, EIA/TIA 568-C
- General properties:
- Suitable for 483 mm (19") cabinet mounting
- Suitable for shielded Digitus® Keystone Modules and Couplers
- Central ground connection
- Technical properties:

- Housing material: 1.5 mm SPCC cold rolled stell sheet, powder-coated
- Material standard: EN 10 130(1991), BS 1449, NFA 36/401, DIN 1623, UNI 5866, UNE 36-086, SIS, JIS G 3141, ASTM, SAE, NFA 36/401
- Grounding bar material: Galvanized steel
- Physical properties:
- Operation temperature: -20° C to +70 °C (ISO/IEC 11801, EN 50173-1, ANSI/TIA/EIA 568 C)
- Operation temperature: -20° C to +70 °C (ISO/IEC 11801, EN 50173-1, ANSI/TIA/EIA 568 C)
- Color: light grey, RAL 7035
- Units: 1
- Ports: 24

Logistics						
	Number (pcs)	Weight (kg)	Depth (cm)	Width (cm)	Height (cm)	cm³
Packaging Unit Carton	15	13.02	58.00	53.00	24.00	73,776.00
Packaging Unit Inside	1	0.87	7.30	56.50	10.00	4,124.50
Packaging Unit Single	1	0.87	7.30	56.50	10.00	4,124.50
Net single without Packaging	1	0.77	7.30	56.50	10.00	4,124.50

More images:

