



USB-C Docking Station Alt-Mode and Pass through Power Delivery Charging

DOCKUCPT01

SKU: 8NV757

The DOCKUCPT01 USB-C Pass Through Docking Station from V7 allows you to add up to 3 displays, Audio, Gigabit Ethernet, SD/Micro SD/MMC memory cards, and extra USB ports to almost any USB-C enabled device. It features HDMI, DisplayPort and VGA display outputs that can be used to expand or mirror your device for multitasking productivity. It has a USB-C PD charging port to connect a USB-C Power supply which can supply up to 100 Watts of USB-C Charging to your computer at the same time as providing all the extra connectivity. It is compatible with DisplayPort Alt mode, USB-C and Thunderbolt(tm) 3 host computers, mobile devices, or other devices.

- Easily connect your displays and peripherals to your laptop with one USB-C Cable
- Adds HDMI, DisplayPort, and VGA display connections, Secure Digital (SD) and Micro SD slots, Gigabit Ethernet, Audio, and extra USB ports simultaneously
- The USB-C cable can be routed through the bottom of the docking station for maximum flexibility
- USB-C PD pass through charging of your device up to 100 Watts (20V/5A) with fast role swap
- Rest your laptop on top of the docking station for ventilation and to save desktop space

General

Sku: 8NV757
 Model: DOCKUCPT01
 EAN: 0662919111934
 Warranty: 2 years
 Compliance: CE, FCC, UKCA
 Country Of Origin: Vietnam
 Package Type: 4 Color Box
 SAP: 5085780
 Package Includes: Dock, USB-C Cable, User Manual, Warranty

Color

Color: Black

Design

Docking Type: USB-C Alt Mode
 Number of Ports: 1 x 3.5 mm Audio Out, 1 x DisplayPort, 1 x HDMI, 1 x RJ45 Ethernet, 1 x VGA port, 1 x 3.5 mm Audio In (Microphone), 2 x USB, 2 x USB-C
 Material: ABS

Package Dimensions

Package Dimensions (L/W/H): 15.35 x 4.53 x 1.38 in
 (390 x 115 x 35 mm)
 Shipping Weight: 0.44 lbs (0.19784 kg)

Product Dimensions

Product Dim (L/W/H): 13.76 x 2.91 x 0.71 in (349.5 x 74 x 18 mm)
 Product Weight: 0.55 lbs (0.2473 kg)

Technical

Connectivity: USB-C
 Maximum Output Power: 20V 5A
 USB Display Type: Alt-Mode
 Connectors: 3.5mm Audio, DisplayPort, HDMI, RJ45, USB 3.1, USB 2.0, USB C, VGA
 Storage Temperature : -10 to 70 C
 Input Voltage: USB-C PD Charging 20V 5A DC
 Security: K Lock Interface
 Operating Temperature : 0 to 45 C
 Output Voltage: DC 20V 5A
 Audio Channel: Combo Audio
 Dock Max Resolution: Support HDMI max 4k/30Hz ;
 VGA max 1920x1200/60Hz; Support DP max 4K/30Hz
 Data Transfer Rate: 1 Gbps



Specifications

SST Mode (Single Stream Transport)			
Ports	VGA	HDMI	DP
1	1080P/60Hz	n/a	n/a
	n/a	4K/30Hz	n/a
	n/a	n/a	4K/30Hz
2	1080P/60Hz	1080P/60Hz	n/a
	1080P/60Hz	n/a	1080P/60Hz
	n/a	4K/30Hz	4K/30Hz
3	1080P/60Hz	1080P/60Hz	1080P/60Hz

MST Mode (Multi-Stream Transport)			
Ports	VGA	HDMI	DP
1	1080P/60Hz	n/a	n/a
	n/a	4K/30Hz	n/a
	n/a	n/a	4K/30Hz
2	1080P/60Hz	1080P/60Hz	n/a
	1080P/60Hz	n/a	1080P/60Hz
	n/a	1080P/60Hz	1080P/60Hz
3	1080P/60Hz	720p/60Hz	720p/60Hz
	720p/60Hz	720p/60Hz	1080P/60Hz
	720p/60Hz	1080P/60Hz	720p/60Hz