





D0S-2312-G



Ordering information

Туре	Part no.
D0S-2312-G	6027538


Other models and accessories -> www.sick.com/

Detailed technical data

Technical specifications

cessory group	Plug connectors and cables
cessory family	Field-attachable connectors
onnection type head A	Female connector, M23, 12-pin, straight
nnection type head B	-
onnection type	Solder connection
cking plug connector	Quick screw connection
nnector material	Zinc die-cast, nickel-plated
nnector color	Nickel-plated
cking nut material	Zinc die-cast, nickel-plated
ielding	Shielded
rmitted cable diameter	5.5 mm 10.5 mm
ference voltage	≤ 160 V
irrent loading	7 A
gnal type	HIPERFACE [®] , SSI, Incremental
closure rating	IP66/ IP67
escription	Head A: female connector, M23, 12-pin, straight, shielded, for cable diameter 5.5 mm 10.5 mm Head B: Operating temperature: –20 $^\circ C$ +130 $^\circ C$
nbient operating temperature	
Head	-20 °C +130 °C

Dimensional drawing (Dimensions in mm (inch))



- 1) Purple1) Orange/black

SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is "Sensor Intelligence."

WORLDWIDE PRESENCE:

Contacts and other locations -www.sick.com



Online data sheet

