


Original line

DRB-0805HD









Crimp profile

DRB-0805HD is a precision, ratchet crimp tool designed to provide consistent and reliable crimp connections on Open barrel on wires ranging from .

Easy to use

Open the tool. Insert terminal in correct nest. Close tool until terminal fastened. Insert wire into terminal. Close tool until ratchet release. Attention: To release ratchet mechanism, push the trigger.

Calibration

To calibrate this tool the pre-load has to be measured. Gauge is required to ensure that the die is according to specification. For more information; See instruction sheet.

- Compact, pocketable design.
- Ergonomic handles for low effort crimping.
- Ratchet action to ensure full crimp cycle with safety release.
- Durable minimum of 50,000 cycles.
- Tool is factory set with a precise eccentric cam adjustment function to quarantee performance.

Technical data

Prod.code: DRB-0805HD Lenght: 198 mm / 7,80" Height: 65 mm / 2,56" Weight: 350 gr / 0,77 lbs Connector: Open barrel

Description: Open barrel / Uninsulated

Wire size: 28-20 AWG

Distributors address info