




**202708**  
**OGUTI 005/100 FP3K-TSSL**  
**Optical label sensor**

- Fast, simple, safe: Sensitivity adjustment via teach key
- Auto-teach during a running process
- Remote teach option with key-lock function
- LED indicator for the teach procedure
- Large insertion depth for ideal probing position
- Detection of even the smallest objects
- Large functional reserve
- Light/dark switching
- 5-year warranty



Function										

Technical data (typ.)	+20°C, 24 V DC
Service voltage	10 ... 35 V DC (Supply Class 2)
No-load current (max.)	35 mA
Insulation voltage endurance	500 V
Leg length internal	100 mm
Housing dimensions	35 x 120 x 14 mm
Housing length	120 mm
Housing height	35 mm
Housing width	14 mm
Housing material	Die-cast zinc (Black, painted)
Protection class	III, operation on protective low voltage
Operating principle	Optical
Evaluation	digital
Design	Fork
Switching output	pnp, 200 mA, NO/NC, switchable
Voltage drop (max.)	2 V
Light source	LED
Color	Infrared
Wavelength	880 nm
Modulation	Clocked
Ambient light immunity	40 kLx
Fork opening	5 mm



**202708**  
**OGUTI 005/100 FP3K-TSSL**  
**Optical label sensor**

<b>Technical data (typ.)</b>	<b>+20°C, 24 V DC</b>
Resolution	Ø 0,5 mm
Switching hysteresis (max.)	0,1 mm
Reproducibility	< 0,03 mm
Sensitivity adjustment	Teach button, Remote teach
Switching frequency	3.000 Hz
Ambient temperature during operation	-10 ... +60 °C
Protection type	IP 67
Connection	Connector, M8, 4-pin
Connection cable	TK ...
<b>More information / accessories</b>	<b><a href="https://www.di-soric.com/202708">https://www.di-soric.com/202708</a></b>