


Dimensions are shown in mm


76A/LR44

Zinc/Manganese Dioxide Battery



	The same of the sa
.000 .014	Nominal V
.000 .012	Rated Cap
.000	
.010	Average V
	Terminals
	Operating Range:
	NEDA/ANS
	I

SPECIFICATIONS	
Nominal Voltage:	1.5 V
Rated Capacity:	105 mAh on 6.8 kΩ to 1.2 V
Average Weight:	1.98 g (0.070 oz.)
Terminals:	Flat
Operating Temp. Range:	-20°C – 54°C (-4°F – 130°F)
NEDA/ANSI: IEC:	1166A LR44



DURACEL

Berkshire Corporate Park Bethel, CT. 06801 U.S.A. Telephone: Toll-free 1-800-544-5454

www.duracell.com

Delivered capacity is dependent on the applied load, operating temperature and cut-off voltage. Please refer to the charts and discharge data shown for examples of the energy/service life that the battery will provide for various load conditions.