

E219-3D



Products Low Voltage Products and Systems Modular DIN Rail Products Modular DIN Rail Components MDRCs
Command Devices

General Information

| | |
|-------------------------------|---|
| Extended Product Type: | E219-3D |
| Product ID: | 2CCA703901R0001 |
| EAN: | 7612271413316 |
| Catalog Description: | E219-3D |
| Long Description: | multi indicator light with 3 green LEDs Voltage range = 415-230 VACPDC Module width 0,5 |

Additional Information

| | |
|---|---|
| Color: | Green, green, green |
| Country of Origin: | Switzerland (CH) |
| Customs Tariff Number: | 85365053 |
| Data Sheet, Technical Information: | 2CCC441003C0101 |
| Declaration of Conformity - CE: | 2CCC441003D0601 |
| EAN: | 7612271413316 |
| ETIM 4: | EC001657 - Indicator light for distribution board |
| ETIM 5: | EC001657 - Indicator light for distribution board |
| ETIM 6: | EC001657 - Indicator light for distribution board |
| Environmental Information: | 2CCC441002C0201 |
| Instructions and Manuals: | 2CCC441001C0201 |
| Invoice Description: | E219-3D |
| Minimum Order Quantity: | 10 piece |
| Number of LEDs: | 3 |
| Object Classification Code: | P |
| Package Level 1 EAN: | 7612271413316 |
| Package Level 1 Gross Weight: | 471.2 g |
| Package Level 1 Height: | 76 mm |
| Package Level 1 Length: | 92.5 mm |
| Package Level 1 Units: | 1 piece |
| Package Level 1 Width: | 96 mm |
| Power Loss: | 1.2 W |
| Product Main Type: | E219 Control Switches, Pushbuttons and Indicator Lights |
| Product Name: | Indicator Light |
| Product Net Depth: | 58 mm |
| Product Net Height: | 85 mm |
| Product Net Length: | 92.5 mm |
| Product Net Weight: | 0.044 kg |
| Product Net Width: | 9 mm |
| Rated Operational Voltage: | 415 / 230 V AC |
| RoHS Information: | 2CCC441008D0201 |
| RoHS Status: | Following EU Directive 2002/95/EC August 18, 2005 and amendment |
| Selling Unit of Measure: | piece |
| Short Description: | E219-90-10C3D Indicator light with 3 green LEDs 415/230VAC |
| Standards: | EN 62094-1 |
| Voltage Range: | 230 ... 415 V AC |
| Width in Number of Modular Spacings: | 0.5 |

