

# E219-D



Products Low Voltage Products and Systems Modular DIN Rail Products Modular DIN Rail Components MDRCs  
Command Devices

## General Information

<b>Extended Product Type:</b>	E219-D
<b>Product ID:</b>	2CCA703402R0001
<b>EAN:</b>	7612270939305
<b>Catalog Description:</b>	E219-D
<b>Long Description:</b>	Indicator light with maintenance-free LED, LED colour: green 115-250 VACPDC, 12-48 VA CDCPDC, 110-220 VDCPDC Module width 0,5

## Additional Information

<b>Color:</b>	Green
<b>Country of Origin:</b>	Switzerland (CH)
<b>Customs Tariff Number:</b>	85365053
<b>Data Sheet, Technical Information:</b>	2CCC441003C0101
<b>Declaration of Conformity - CE:</b>	2CCC441003D0601
<b>E-nummer:</b>	2102813
<b>EAN:</b>	7612270939305
<b>ETIM 4:</b>	EC001657 - Indicator light for distribution board
<b>ETIM 5:</b>	EC001657 - Indicator light for distribution board
<b>ETIM 6:</b>	EC001657 - Indicator light for distribution board
<b>Environmental Information:</b>	2CCC441002C0201
<b>Instructions and Manuals:</b>	2CCC441001C0201
<b>Invoice Description:</b>	E219-D
<b>Minimum Order Quantity:</b>	10 piece
<b>Number of LEDs:</b>	1
<b>Object Classification Code:</b>	P
<b>Package Level 1 EAN:</b>	7612270939305
<b>Package Level 1 Gross Weight:</b>	431.2 g
<b>Package Level 1 Height:</b>	76 mm
<b>Package Level 1 Length:</b>	92.5 mm
<b>Package Level 1 Units:</b>	1 piece
<b>Package Level 1 Width:</b>	96 mm
<b>Power Loss:</b>	0.56 W
<b>Product Main Type:</b>	E219 Control Switches, Pushbuttons and Indicator Lights
<b>Product Name:</b>	Indicator Light
<b>Product Net Depth:</b>	58 mm
<b>Product Net Height:</b>	85 mm
<b>Product Net Length:</b>	92.5 mm
<b>Product Net Weight:</b>	0.040 kg
<b>Product Net Width:</b>	9 mm
<b>Rated Operational Voltage:</b>	115 ... 230 V
<b>RoHS Information:</b>	2CCC451021D0201
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment
<b>Selling Unit of Measure:</b>	piece
<b>Short Description:</b>	E219-40-10C219-D Indicator light green LED 115 ... 250VAC
<b>Standards:</b>	EN 62094-1
<b>Voltage Range:</b>	115 ... 250 V AC
<b>Width in Number of Modular Spacings:</b>	0.5

