

## Easy UPS 3S High Capacity Battery String

### E3SBTH4

Call for More Information 800 10 436



- High capacity battery string for use with Easy UPS 3S with internal battery slots and Easy UPS 3S Empty Modular Battery Cabinet (E3SXR6). Each battery string consists of four 9 Ah battery modules (E3SBTHU).

#### Output

Battery Output Voltage	120 V
------------------------	-------

#### Batteries & Runtime

Battery type	VRLA
Battery mounting	Enclosed battery cartridge
Battery Design Life	3 - 5

#### Physical

Maximum Height	157MM, 15.7CM
Maximum Width	428MM, 42.8CM
Maximum Depth	760MM, 76.0CM
Net Weight	108.0KG
Shipping weight	112.0KG
Shipping Height	180MM, 18.0CM
Shipping Width	820MM, 82.0CM
Shipping Depth	560MM, 56.0CM

#### Environmental

Operating Temperature	0 - 40 °C
Operating Relative Humidity	0 - 95 (Non-condensing) %
Operating Elevation	0 - 1000.05meters
Storage Temperature	-15 - 40 °C

Disclaimer: Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.

## Technical Specifications

Easy UPS 3S High Capacity Battery String | E3SBTH4 | Downloaded on 10/12/2023 (EST)

Environmental	
Storage Relative Humidity	0 - 95 (Non-condensing) %
Storage Elevation	0 - 15240meters

Sustainable Offer Status	
RoHS	Compliant
Other Environmental Compliance	China RoHS

**Disclaimer:** Documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user's applications.