

Product datasheet

Specifications



Easy UPS 3S Battery Breaker Box

Local distributor code: 422504016 E3SOPT007

Overview

Presentation	Wall mounted battery breaker box for use with third party battery solutions.
Lead time	Usually Ships within 6 Weeks

Main

Battery type	VRLA
--------------	------

Batteries & Runtime

Number of battery filled slots	0
Number of battery free slots	0

Physical

Height	65 cm
Width	50 cm
Depth	28 cm
Net weight	25 kg
Mounting mode	Not rack-mountable

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...3333 ft
Ambient air temperature for storage	-15...40 °C
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0.00...15240.00 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	122 cm

Package 1 Width	51 cm
Package 1 Length	85 cm
Package 1 Weight	46.5 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)