

# Product datasheet

Specifications



## Easy UPS 3S 10 kVA 400 V 3:3 UPS for external batteries

E3SUPS10KH

### Overview

**Presentation** High-efficiency 3-phase UPS that features advanced product features, competitive specifications, and robust electrical design, making business continuity easy in the data center or electrical room. This is an exceptionally easy to install, operate, maintain, and service 10 kVA UPS, ideal for small and medium businesses. Includes dust filter and conformance-coated boards for harsh environments. This UPS is supplied without batteries, so you can easily customize the battery solution.

**Lead time** Usually Ships within 6 Weeks

### Main

**Main Input Voltage** 400 V 3 phases

**Other Input Voltage** 380 V  
415 V

**Main Output Voltage** 400 V 3 phases

**Other Output Voltage** 380 V  
415 V

**Rated power in W** 10 kW

**Rated power in VA** 10 kVA

**Provided equipment** Dust filter  
Installation guide

### Batteries & Runtime

**Battery type** External battery system

**Maximum short-circuit current** 10 kA

**Number of battery filled slots** 0

**Number of battery free slots** 0

### Physical

**Colour** White (RAL 9003)

**Height** 53 cm

**Width** 25 cm

**Depth** 70 cm

**Net weight** 36 kg

**USB compatible** Yes

## Input

Maximum input current	18 A
Input harmonic distortion	Less than 3 % for full load
Load power factor	0.9 leading to 0.9 lagging
Input Power Factor at Full Load	0.99
Input voltage limits	304...477 V
Network frequency	45...65 Hz

## Output

Maximum configurable power in VA	10 kVA
Maximum configurable power in W	10 kW
Output frequency	50 Hz sync to mains 60 Hz sync to mains
Harmonic distortion	Less than 3 %
Output harmonic distortion	< 3% linear load
Output overload operation	10 minutes at 125% and 60 seconds at 150%
UPS type	Double conversion online
Bypass type	Built-in maintenance bypass
Crest factor	3 : 1

## Conformance

Product certifications	CE EAC RCM
------------------------	------------------

## Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...3281 ft
Ambient air temperature for storage	-15...40 °C
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0.00...14999.82 m
Acoustic level	60 dBA
Heat dissipation	516 Btu/h
IP degree of protection	IP20

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	77.2 cm
Package 1 Width	70 cm
Package 1 Length	40 cm
Package 1 Weight	50 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

## Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

## Recommended replacement(s)