

Product datasheet

Specifications



Easy UPS 3S 30 kVA 400V 3:3 UPS, 2 internal 7Ah modular battery strings, expandable to 4

E3SUPS30KHB1

Overview

Presentation Easy-to-install, easy-to-operate, easy-to-maintain, and easy-to-service 30 kVA, 400V 3-phase UPS. With advanced product features, competitive specifications, and robust electrical design, the Easy UPS 3S UPS makes business continuity easy for small and medium data centers and electrical rooms. Includes dust filter and conformance-coated boards for harsh environments, and 2 internal 7Ah modular battery strings, expandable to 4 strings for extended runtime.

Lead time Usually Ships within 6 Weeks

Main

Main Input Voltage 400 V 3 phases

Other Input Voltage 380 V
415 V

Main Output Voltage 400 V 3 phases

Other Output Voltage 380 V
415 V

Rated power in W 30 kW

Rated power in VA 30 kVA

Provided equipment Dust filter
Installation guide

Batteries & Runtime

Battery type VRLA

Battery voltage 240 V

Maximum short-circuit current 10 kA

Number of battery filled slots 2

Number of battery free slots 2

Physical

Colour White (RAL 9003)

Height 140 cm

Width 50 cm

Depth 96.9 cm

Net weight 584 kg

USB compatible Yes

Input

Maximum input current	55 A
Input harmonic distortion	Less than 3 % for full load
Load power factor	0.9 leading to 0.9 lagging
Input Power Factor at Full Load	0.99
Input voltage limits	304...477 V
Network frequency	45...65 Hz

Output

Maximum configurable power in VA	30 kVA
Maximum configurable power in W	30 kW
Output frequency	50 Hz sync to mains 60 Hz sync to mains
Harmonic distortion	Less than 3 %
Output harmonic distortion	< 3% linear load
Output voltage tolerance	+/- 1.5 %
UPS type	Double conversion online
Additional information	UPS weight does not include battery weight.

Conformance

Product certifications	CE EAC RCM
------------------------	------------------

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...3333 ft
Ambient air temperature for storage	-15...40 °C
Storage Relative Humidity	0...95 % non-condensing
Storage altitude	0.00...15240.00 m
Acoustic level	63 dBA
Heat dissipation	1410 Btu/h
IP degree of protection	IP20

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	164 cm
Package 1 Width	111.4 cm
Package 1 Length	68.3 cm
Package 1 Weight	638 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

Recommended replacement(s)